

Valves and solenoid valves - Series D (VA)

Product code: D43VA-MR-FS

Datasheet creation date: 10/03/2025 11:23

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	D
Size (mm)	4 = 25 mm
Actuation	3 = electric 15 mm
Component	VA = Valve with threaded body
Type of solenoid valve	M = 5/2 Monostable
Type of manual override	R = with push and turn device
Connection	FS = Ø14 fittings S6510 14-3/8 + silencers 2921 3/8

Valves and solenoid valves - Series D (VA)

Product code: D43VA-MR-FS



DIMENSIONS

Series	D
Size (mm)	4 = 25 mm
Actuation	3 = electric 15 mm
Component	VA = Valve with threaded body
Type of solenoid valve	M = 5/2 Monostable
Type of manual override	R = with push and turn device
Connection	FS = Ø14 fittings S6510 14-3/8 + silencers 2921 3/8