

## Direct acting solenoid valves - Series KL

Product code: KL040-A63AY-M3P

Datasheet creation date: 10/03/2025 11:34

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	KL = standard
<b>Valvebody</b>	0 = 3/2 body - ISO 15218
<b>Functions</b>	4 = 3/2 NC
<b>Ports</b>	0 = on sub-base or manifold
<b>Diameter</b>	A6 = Ø0.60 mm
<b>Seals material</b>	3 = FKM
<b>Body material</b>	A = PBT
<b>Manual Override</b>	Y = monostable
<b>Electric connection</b>	M = M8 connector - 3 pins
<b>Voltage Power</b>	3 = 24V DC - 1W
<b>Fixing</b>	P = fixing screws for plastic
<b>Option</b>	= standard

## Direct acting solenoid valves - Series KL

Product code: KL040-A63AY-M3P



### DIMENSIONS

<b>Series</b>	KL = standard
<b>Valvebody</b>	0 = 3/2 body - ISO 15218
<b>Functions</b>	4 = 3/2 NC
<b>Ports</b>	0 = on sub-base or manifold
<b>Diameter</b>	A6 = Ø0.60 mm
<b>Seals material</b>	3 = FKM
<b>Body material</b>	A = PBT
<b>Manual Override</b>	Y = monostable
<b>Electric connection</b>	M = M8 connector - 3 pins
<b>Voltage Power</b>	3 = 24V DC - 1W
<b>Fixing</b>	P = fixing screws for plastic
<b>Option</b>	= standard