

## Direct acting solenoid valves - Series KL

Product code: KL210-A83A0-1BM

Datasheet creation date: 10/03/2025 11:33

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	KL = standard
<b>Valvebody</b>	2 = 2/2 body
<b>Functions</b>	1 = 2/2 NC
<b>Ports</b>	0 = on sub-base or manifold
<b>Diameter</b>	A8 = Ø0.80 mm
<b>Seals material</b>	3 = FKM
<b>Body material</b>	A = PBT
<b>Manual Override</b>	0 = not requested or not foreseen
<b>Electric connection</b>	1 = 90 ° connector with protection and led
<b>Voltage Power</b>	B = 12V DC - 1.3/0.3W
<b>Fixing</b>	M = fixing screws for metal
<b>Option</b>	= standard

## Direct acting solenoid valves - Series KL

Product code: KL210-A83A0-1BM



### DIMENSIONS

<b>Series</b>	KL = standard
<b>Valvebody</b>	2 = 2/2 body
<b>Functions</b>	1 = 2/2 NC
<b>Ports</b>	0 = on sub-base or manifold
<b>Diameter</b>	A8 = Ø0.80 mm
<b>Seals material</b>	3 = FKM
<b>Body material</b>	A = PBT
<b>Manual Override</b>	0 = not requested or not foreseen
<b>Electric connection</b>	1 = 90 ° connector with protection and led
<b>Voltage Power</b>	B = 12V DC - 1.3/0.3W
<b>Fixing</b>	M = fixing screws for metal
<b>Option</b>	= standard