

## Pressure regulators - Series MX

Product code: MX2-1/2-M010

Datasheet creation date: 10/03/2025 01:28

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                           |   |
|---------------------------|---|
| <b>Series</b>             | MX  |
| <b>Size</b>               | 2   |
| <b>PORTS (IN - OUT)</b>   | 1/2 = G1/2                                      |
| <b>Type of regulator</b>  | M = Manifold pressure regulator                 |
| <b>Operating pressure</b> | 0 = 0.5 ÷ 10 bar (standard)                     |
| <b>Design type</b>        | 1 = without relieving                           |
| <b>Pressure gauge</b>     | 0 = without pressure gauge (with threaded port) |
| <b>Flow direction</b>     | = from left to right (standard)                 |

## Pressure regulators - Series MX

Product code: MX2-1/2-M010



### DIMENSIONS

|                    |          |
|--------------------|----------|
| <b>A</b>           | G1/2     |
| <b>B (bar)</b>     | 0-12 bar |
| <b>C (mm)</b>      | 70.0     |
| <b>D (mm)</b>      | 45       |
| <b>F (mm)</b>      | M47x1.5  |
| <b>G (mm)</b>      | 70       |
| <b>H (mm)</b>      | 74.5     |
| <b>I (mm)</b>      | 68       |
| <b>M (mm)</b>      | 45       |
| <b>N (mm)</b>      | 166      |
| <b>P (mm)</b>      | 78       |
| <b>Q (mm)</b>      | 5        |
| <b>R (mm)</b>      | 88       |
| <b>S (mm)</b>      | 50.5     |
| <b>T (mm)</b>      | 37.5     |
| <b>U (mm)</b>      | 0±13     |
| <b>Weight (kg)</b> | 0.6      |