

Filter-regulators - Series MX

Product code: MX2-3/8-FR5000

Datasheet creation date: 10/03/2025 01:25

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|-------------------------------|---|
| Series | MX |
| Size | 2 |
| PORTS (IN - OUT) | 3/8 = G3/8 |
| Filter-regulator | FR |
| Filtering element | 5 = 5 µm with relieving and by-pass valve |
| Draining of condensate | 0 = semiautomatic-manual drain (standard - only for polymer bowl) |
| Operating pressure | 0 = 0.5 ÷ 10 bar (standard) |
| Pressure gauge | 0 = without pressure gauge (with threaded port) |
| Flow direction | = from left to right (standard) |

Filter-regulators - Series MX

Product code: MX2-3/8-FR5000



DIMENSIONS

| | |
|--------------------|----------|
| A | G3/8 |
| B (bar) | 0-12 bar |
| C (mm) | 70.0 |
| D (mm) | 45 |
| E (mm) | Ø4.5 |
| E2 (mm) | 9.5 |
| F (mm) | M47x1.5 |
| G (mm) | 55.5 |
| H (mm) | 74.5 |
| I (mm) | 68 |
| L | G 1/8 |
| M (mm) | 80 |
| N (mm) | 290 |
| O (mm) | 127 |
| P (mm) | 78 |
| Q (mm) | 5 |
| R (mm) | 85 |
| S (mm) | 174.5 |
| T (mm) | 37.5 |
| U (mm) | 0÷16 |
| Weight (kg) | 0.8 |