

## Filter-regulators - Series MX

Product code: MX3-3/4-FR1300

Datasheet creation date: 10/03/2025 01:26

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                               |   |
|-------------------------------|---|
| <b>Series</b>                 | MX  |
| <b>Size</b>                   | 3   |
| <b>PORTS (IN - OUT)</b>       | 3/4 = G3/4                                      |
| <b>Filter-regulator</b>       | FR  |
| <b>Filtering element</b>      | 1 = 5 µm with relieving                         |
| <b>Draining of condensate</b> | 3 = automatic drain                             |
| <b>Operating pressure</b>     | 0 = 0.5 ÷ 10 bar (standard)                     |
| <b>Pressure gauge</b>         | 0 = without pressure gauge (with threaded port) |
| <b>Flow direction</b>         | = from left to right (standard)                 |

## Filter-regulators - Series MX

Product code: MX3-3/4-FR1300



### DIMENSIONS

|                    |          |
|--------------------|----------|
| <b>A</b>           | G3/4     |
| <b>B (bar)</b>     | 0-12 bar |
| <b>C (mm)</b>      | 89.5     |
| <b>D (mm)</b>      | 54       |
| <b>E (mm)</b>      | Ø4       |
| <b>E2 (mm)</b>     | 8.0      |
| <b>F (mm)</b>      | M57x1.5  |
| <b>G (mm)</b>      | 61.5     |
| <b>H (mm)</b>      | 81.0     |
| <b>I (mm)</b>      | 76       |
| <b>L</b>           | G 1/8    |
| <b>M (mm)</b>      | 95       |
| <b>N (mm)</b>      | 345      |
| <b>O (mm)</b>      | 142      |
| <b>P (mm)</b>      | 104      |
| <b>Q (mm)</b>      | 5        |
| <b>R (mm)</b>      | 99       |
| <b>S (mm)</b>      | 196.5    |
| <b>T (mm)</b>      | 44.5     |
| <b>U (mm)</b>      | 0÷20     |
| <b>Weight (kg)</b> | 1.3      |