

## Open Frame Controller modular proportional regulator - Series OF

Product code: OF-0H11-FFW2-F-0-00-OX1

Datasheet creation date: 20/05/2026 08:33

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>SERIE (Series)</b>	Open Frame
<b>IELETRICA (Electrical interface)</b>	0 = 0 ÷ 10V analog, 24V power supply
<b>FDCONTROLLO (Control function)</b>	H = 2way high flow pressure control (parallel) Head & Expansion
<b>TAGLIA (Size)</b>	1 = size 37 mm
<b>ATTACCHI (Ports)</b>	1 = G1/8
<b>VALVOLAHEAD (Head valve size)</b>	F = Ø 1mm
<b>VALVOLAEXPANSIO (Expansion valve size)</b>	F = Ø 1mm
<b>GUARNIZIONI (Sealing material)</b>	W = FKM
<b>MATCORPO (Body material)</b>	2 = brass/aluminium
<b>SENSOREHEAD (Relative sensor full scale - Head module)</b>	F = 10 bar
<b>PRESSIONEHEAD (Maximum pressure differential sensor - Head module)</b>	0 = no DP sensor
<b>UGELLOHEAD (Calibrated Nozzle Size - Head Module)</b>	00 = without nozzle
<b>USOCONOX (Use with oxygen)</b>	OX1 = for use with oxygen - cleanliness level according to ASTM G93-03 Standard Level E

## Open Frame Controller modular proportional regulator - Series OF

Product code: OF-0H11-FFW2-F-0-00-OX1



### DIMENSIONS

	M12 5 PIN (Maschio)
	M12 5 PIN (Maschio)
	Micro USB
	G1/8
	G1/8
	G1/8
	Filetto M4 per fissaggio