

Open Frame Controller modular proportional regulator - Series OF

Product code: OF-0N11-H0W2-F-0-00-OX1

Datasheet creation date: 20/05/2026 08:26

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|---|---|
| SERIE (Series) | Open Frame |
| IELETRICA (Electrical interface) | 0 = 0 ÷ 10V analog, 24V power supply |
| FDCONTROLLO (Control function) | N = Pressure, 2way closed loop, Head |
| TAGLIA (Size) | 1 = size 37 mm |
| ATTACCHI (Ports) | 1 = G1/8 |
| VALVOLAHEAD (Head valve size) | H = Ø 1,2mm |
| VALVOLAEXPANSIO (Expansion valve size) | 0 = without Expansion valve |
| GUARNIZIONI (Sealing material) | W = FKM |
| MATCORPO (Body material) | 2 = brass/aluminium |
| SENSOREHEAD (Relative sensor full scale - Head module) | F = 10 bar |
| PRESSIONEHEAD (Maximum pressure differential sensor - Head module) | 0 = no DP sensor |
| UGELLOHEAD (Calibrated Nozzle Size - Head Module) | 00 = without nozzle |
| USOCONOX (Use with oxygen) | OX1 = for use with oxygen - cleanliness level according to ASTM G93-03 Standard Level E |

Open Frame Controller modular proportional regulator - Series OF

Product code: OF-0N11-H0W2-F-0-00-OX1



DIMENSIONS

| | |
|--|--------------------------|
| | M12 5 PIN (Maschio) |
| | M12 5 PIN (Maschio) |
| | Micro USB |
| | G1/8 |
| | G1/8 |
| | G1/8 |
| | Filetto M4 per fissaggio |