

Elettrovalvole a comando diretto - Serie P

Product code: P000-403-E53-OX1

Datasheet creation date: 10/03/2025 11:39

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	P
Body execution	0 = interface
Number of seats	00 = ISO 15218 interface
Number of ways - Functions	4 = 3/2 way - NO
Valve connections	0 = ISO 15218 interface
Orifice diameter	3 = Ø 1.5 mm
Materials	E = PBT body - EPDM seals
Electrical connection	5 = industrial standard (9.4 mm)
Voltage - Absorbed power	3 = 24 V DC - 2 W
Fixing	= fixing screws for metal
Options	OX1 = for oxygen (non-volatile residue less than 550 mg / m ²)

Elettrovalvole a comando diretto - Serie P

Product code: P000-403-E53-OX1



DIMENSIONS

Series	P
Body execution	0 = interface
Number of seats	00 = ISO 15218 interface
Number of ways - Functions	4 = 3/2 way - NO
Valve connections	0 = ISO 15218 interface
Orifice diameter	3 = Ø 1.5 mm
Materials	E = PBT body - EPDM seals
Electrical connection	5 = industrial standard (9.4 mm)
Voltage - Absorbed power	3 = 24 V DC - 2 W
Fixing	= fixing screws for metal
Options	OX1 = for oxygen (non-volatile residue less than 550 mg / m ²)