

## Direct acting solenoid valves - Series PD

Product code: PD000-2A2-F55-OX2

Datasheet creation date: 20/05/2026 04:06

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series</b>	PD
<b>Body execution</b>	0 = single body
<b>Number of seats</b>	00 = interface
<b>Number of ways - Functions</b>	2 = 2/2 way - NC
<b>Material - Body connections</b>	A = aluminum body - side interface
<b>Orifice diameter</b>	2 = Ø 1.2 mm
<b>kv (l/min)</b>	0.54
<b>Seal material</b>	F = FKM
<b>Electrical connection</b>	5 = industry standard (9.4 mm)
<b>Voltage - Absorbed power</b>	5 = 24 V DC - 2 W
<b>Fixing</b>	= fixing screws for metal or clips for sub-base
<b>Use with oxygen</b>	OX2 = for use with oxygen – cleanliness level according to ASTM G93-03 Standard Level B

## Direct acting solenoid valves - Series PD

Product code: PD000-2A2-F55-OX2



### DIMENSIONS

<b>Series</b>	PD
<b>Body execution</b>	0 = single body
<b>Number of seats</b>	00 = interface
<b>Number of ways - Functions</b>	2 = 2/2 way - NC
<b>Material - Body connections</b>	A = aluminum body - side interface
<b>Orifice diameter</b>	2 = Ø 1.2 mm
<b>kv (l/min)</b>	0.54
<b>Seal material</b>	F = FKM
<b>Electrical connection</b>	5 = industry standard (9.4 mm)
<b>Voltage - Absorbed power</b>	5 = 24 V DC - 2 W
<b>Fixing</b>	= fixing screws for metal or clips for sub-base
<b>Use with oxygen</b>	OX2 = for use with oxygen – cleanliness level according to ASTM G93-03 Standard Level B