

Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A025A020

Datasheet creation date: 09/03/2025 23:08

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|--|
| Series | QC |
| Version | B = linear ball bearings |
| Operation | 2 = double acting |
| Materials | A = anodized aluminium body rolled stainless steel 303 piston rod hardened steel C50 columns for QCB |
| Diameter (mm) | 25 |
| Construction | A = standard |
| Stroke type | standard |
| Stroke (mm) | 20 |

Cylinders with integrated guide - Series QCT QCB

Product code: QCB2A025A020



DIMENSIONS

| | |
|----------------|-------|
| L3 (mm) | 74.5 |
| C (mm) | 12 |
| B (mm) | 21.0 |
| O2 (mm) | 24 |
| O4 (mm) | 29 |
| A (mm) | 10 |
| D (mm) | 12 |
| E1 (mm) | 78 |
| E2 (mm) | 26 |
| F | G 1/8 |
| F1 (mm) | 11.5 |
| F2 (mm) | 8.0 |
| F3 (mm) | 28.5 |
| F4 (mm) | 12.5 |
| F5 (mm) | 13.5 |
| F6 (mm) | 11.5 |
| G1 (mm) | 91 |
| G2 (mm) | 40 |
| H (mm) | 82 |
| H1 (mm) | 64 |
| L1 (mm) | 37.5 |
| L2 (mm) | 53.5 |
| M1 (mm) | 93 |

| | |
|-------------------|------|
| M2 (mm) | 42 |
| N (mm) | 30 |
| O1 (mm) | 17 |
| O3 (mm) | 34 |
| P1 | M6x1 |
| P2 | M6x1 |
| P3 | M6x1 |
| Q (mm) | 15 |
| R (mm) | 12 |
| heavy (mm) | 6 |
| Y (mm) | 34 |
| Y1 (mm) | 4 |
| Y2 (mm) | 4.5 |
| Y3 (mm) | 3 |
| Y4 (mm) | 6 |
| X (mm) | 5.5 |
| X1 (mm) | 9 |
| X2 (mm) | 5.0 |
| J (mm) | 50 |
| K | M5 |