

## Short-stroke cylinders - Series QL

Product code: QLN2A080A020

Datasheet creation date: 07/03/2025 14:31

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                          |   |
|--------------------------|---|
| <b>Series</b>            | QL  |
| <b>Version</b>           | N = Non magnetic                            |
| <b>Function</b>          | 2 = double - acting                         |
| <b>Materials</b>         | A = rolled stainless steel rod - AL profile |
| <b>Construction type</b> | A = Standard                                |
| <b>Diameter (mm)</b>     | Ø80   |
| <b>Stroke (mm)</b>       | 20  |
| <b>Rod</b>               | = Standard                                  |
| <b>Certification</b>     | = Standard                                  |

## Short-stroke cylinders - Series QL

Product code: QLN2A080A020



### DIMENSIONS

|         |          |
|---------|----------|
| C (mm)  | 25       |
| D (mm)  | 104.0    |
| E (mm)  | 98.0     |
| G (mm)  | 43.5     |
| H (mm)  | 15.0     |
| H1 (mm) | 12.5     |
| J       | M12x1.75 |
| K (mm)  | 17.5     |
| L (mm)  | 13.5     |
| L1 (mm) | 35.5     |
| M (mm)  | 21       |
| M1 (mm) | 11.0     |
| N (mm)  | 53.5     |
| P       | M16x2    |
| Q       | G3/8     |
| SW (mm) | 22       |
| TG (mm) | 77.0     |
| Z (mm)  | 25       |
| W (mm)  | 45.5     |
| KK      | M22x1.5  |
| AM (mm) | 35.5     |