

Short stroke magnetic cylinders - Series QP-QPR

Product code: QP2A032A030V

Datasheet creation date: 09/03/2025 23:52

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|------------------------|----------------------------|
| Series | QP = standard |
| Diameter (mm) | 32 |
| Operation | 2=double-acting |
| Materials | A = rolled stainless steel |
| Construction | A = standard |
| Stroke type | N = standard |
| Stroke (mm) | 30 |
| Atex | No Atex |
| Rod lenght (mm) | 0 |

Short stroke magnetic cylinders - Series QP-QPR

Product code: QP2A032A030V



DIMENSIONS

| | |
|---------------|-------|
| A (mm) | 45.0 |
| B (mm) | 34.0 |
| B1 (mm) | 32 |
| B2 (mm) | 33 |
| ϕ C (mm) | 12 |
| D (mm) | 55.50 |
| E (mm) | 47.00 |
| G (mm) | 39.5 |
| G1 (mm) | 40 |
| H1 (mm) | 9.5 |
| H (mm) | 9.5 |
| J (mm) | 5.5 |
| J1 | M8 |
| K (mm) | 10.5 |
| L (mm) | 6.0 |
| L1 (mm) | 21.0 |
| M (mm) | 10.0 |
| M1 (mm) | 7.5 |
| N (mm) | 44.0 |
| N1 (mm) | - |
| ϕ O (mm) | 23.5 |
| P | M6 |
| Q | G1/8 |

| | |
|----------------|-------|
| R (mm) | 34.0 |
| R1 (mm) | 36.00 |
| R2 (mm) | 35 |
| SW (mm) | 10 |
| T (mm) | 2.5 |
| U (mm) | - |
| V (mm) | 32.00 |
| AA (mm) | 10 |
| BB (mm) | 6.0 |
| ϕ CC (mm) | 9.0 |
| ϕ DD (mm) | 5.5 |
| EE (mm) | 9.0 |
| FF | M5 |
| LL (mm) | 32.0 |
| MM (mm) | 47.0 |
| NN (mm) | 45 |
| RR (mm) | 36.0 |
| VV (mm) | - |
| Z (mm) | 7.0 |