

Series QX - Twin Cylinders

Product code: QXT3A016A100

Datasheet creation date: 10/03/2025 00:11

Check the most updated document online [click here](#)




TECHNICAL DATA

Series (mm)	QX
Version (mm)	T = sintered bronze bushes
Operation (mm)	3 = through-rod (double-flange), radial pressure supply
Materials (mm)	A = anodized aluminium body, rolled stainless steel 303 piston rod
Diameter (mm)	16
Construction (mm)	A = standard
Stroke cylinder (mm)	100

Series QX - Twin Cylinders

Product code: QXT3A016A100



DIMENSIONS

A (mm)	58
B (mm)	21
C (mm)	56
E (mm)	19
F (mm)	42
G (mm)	5
I (mm)	2.5
M (mm)	10
Q (mm)	11
R (mm)	13
L1 (mm)	86.6
L2 (mm)	111.6
L3 (mm)	34.0
L4 (mm)	8.5
L5 (mm)	20
L6 (mm)	73.3
L7 (mm)	13
L8 (mm)	30
L9 (mm)	126.6
L10 (mm)	146.6
L11 (mm)	52.0
H2 (mm)	4.5
H3 (mm)	4.0

H4 (mm)	5.0
H5 (mm)	6.0
H6 (mm)	6
H7 (mm)	3
H8 (mm)	0.0
H10 (mm)	10.5
H11 (mm)	16.5
H12 (mm)	10.5
H13 (mm)	0
H14 (mm)	5.5
D1	M5
D2 (mm)	7.5
D3 (mm)	2.5
D4 (mm)	M3
D5	M4
D6	M3
D7 (mm)	2.5
D8 (mm)	0
D9 (mm)	0.0
D10	M5
NN (mm)	8
EE	M5
J (mm)	0.0