

## Series QX - Twin Cylinders

Product code: QXT3A032A010

Datasheet creation date: 10/03/2025 00:12

Check the most updated document online [click here](#)




### TECHNICAL DATA

<b>Series (mm)</b>	QX
<b>Version (mm)</b>	T = sintered bronze bushes
<b>Operation (mm)</b>	3 = through-rod (double-flange), radial pressure supply
<b>Materials (mm)</b>	A = anodized aluminium body, rolled stainless steel 303 piston rod
<b>Diameter (mm)</b>	32
<b>Construction (mm)</b>	A = standard
<b>Stroke cylinder (mm)</b>	10

## Series QX - Twin Cylinders

Product code: QXT3A032A010



### DIMENSIONS

A (mm)	94
B (mm)	37
C (mm)	92
E (mm)	35
F (mm)	45
G (mm)	8
I (mm)	4.0
M (mm)	16
Q (mm)	16
R (mm)	18
L1 (mm)	115.6
L2 (mm)	155.6
L3 (mm)	46.5
L4 (mm)	12.0
L5 (mm)	30
L6 (mm)	32.8
L7 (mm)	20
L8 (mm)	30
L9 (mm)	65.6
L10 (mm)	65.6
L11 (mm)	47.0
H2 (mm)	6.5
H3 (mm)	4.0

H4 (mm)	7.5
H5 (mm)	7.5
H6 (mm)	8
H7 (mm)	4
H8 (mm)	0.0
H10 (mm)	8.5
H11 (mm)	28.5
H12 (mm)	8.5
H13 (mm)	20
H14 (mm)	18.5
D1	M8
D2 (mm)	10.5
D3 (mm)	4.0
D4 (mm)	M5
D5	M5
D6	M4
D7 (mm)	4.0
D8 (mm)	0
D9 (mm)	0.0
D10	M6
NN (mm)	16
EE	G1/8
J (mm)	0.0