

## Stopper cylinders - Series ST

Product code: ST312A050A030(60)

Datasheet creation date: 10/03/2025 00:21

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	ST31
<b>Operation</b>	2=double-acting
<b>Design</b>	A = standard
<b>Diameter (mm)</b>	50
<b>Construction</b>	A = standard
<b>Stroke (mm)</b>	30

## Stopper cylinders - Series ST

Product code: ST312A050A030(60)

### DIMENSIONS

AF (mm)	0.0
BG (mm)	21.5
G (mm)	14.5
H1 (mm)	5.7
D (mm)	32
D1 (mm)	53
D2 (mm)	0
D3 (mm)	0
D4 (mm)	6
D5 (mm)	0
D6 (mm)	0
D7	6
E (mm)	68.0
EE	G1/8
E1 (mm)	M3
KF (mm)	0
LA (mm)	6
PL (mm)	8.0
RT	M8
T1 (mm)	0
T2 (mm)	4.5
TG (mm)	50.0
L (mm)	71.0

ZA (mm)	45.5
ZB (mm)	69.5
L1 (mm)	24.0
L2 (mm)	0.0
L3 (mm)	0
L4 (mm)	0
R (mm)	0
P (mm)	0.0
B1 (mm)	0
SW1 (mm)	0.0
T3 (mm)	0.0