

Stopper cylinders - Series ST

Product code: ST322A020F010

Datasheet creation date: 10/03/2025 00:19

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	ST32
Operation	2=double-acting
Design	A = standard
Diameter (mm)	20
Construction	F = female rod thread
Stroke (mm)	10

Stopper cylinders - Series ST

Product code: ST322A020F010

DIMENSIONS

AF (mm)	6.0
BG (mm)	20.0
G (mm)	10.9
H1 (mm)	0.0
D (mm)	12
D1 (mm)	25
D2 (mm)	0
D3 (mm)	0
D4 (mm)	9
D5 (mm)	5
D6 (mm)	9
D7	4
E (mm)	35.8
EE	M5
E1 (mm)	0
KF (mm)	3
LA (mm)	5
PL (mm)	6.5
RT	M5
T1 (mm)	0
T2 (mm)	2.5
TG (mm)	22.0
L (mm)	35.8

ZA (mm)	53.5
ZB (mm)	64.0
L1 (mm)	9.5
L2 (mm)	68.0
L3 (mm)	71
L4 (mm)	73
R (mm)	10
P (mm)	2.0
B1 (mm)	4
SW1 (mm)	10.0
T3 (mm)	1.2