

Stopper cylinders - Series ST

Product code: ST322A050F030(20)

Datasheet creation date: 10/03/2025 00:20

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	ST32
Operation	2=double-acting
Design	A = standard
Diameter (mm)	50
Construction	F = female rod thread
Stroke (mm)	30

Stopper cylinders - Series ST

Product code: ST322A050F030(20)

DIMENSIONS

AF (mm)	14.5
BG (mm)	0.0
G (mm)	14.3
H1 (mm)	0.0
D (mm)	32
D1 (mm)	51
D2 (mm)	40
D3 (mm)	34
D4 (mm)	12
D5 (mm)	12
D6 (mm)	0
D7	6
E (mm)	69.6
EE	G1/8
E1 (mm)	0
KF (mm)	8
LA (mm)	0
PL (mm)	7.6
RT	M8
T1 (mm)	2
T2 (mm)	3.0
TG (mm)	46.5
L (mm)	69.6

ZA (mm)	65.5
ZB (mm)	81.0
L1 (mm)	14.5
L2 (mm)	92.5
L3 (mm)	100
L4 (mm)	105
R (mm)	25
P (mm)	7.0
B1 (mm)	10
SW1 (mm)	28.0
T3 (mm)	2.5