

## Stopper cylinders - Series ST

Product code: ST322R032A020

Datasheet creation date: 10/03/2025 00:17

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	ST32
<b>Operation</b>	2=double-acting
<b>Design</b>	R = anti-rotation
<b>Diameter (mm)</b>	32
<b>Construction</b>	A = standard
<b>Stroke (mm)</b>	20

## Stopper cylinders - Series ST

Product code: ST322R032A020

### **DIMENSIONS**

<b>AF (mm)</b>	11.0
<b>BG (mm)</b>	0.0
<b>G (mm)</b>	14.3
<b>H1 (mm)</b>	0.0
<b>D (mm)</b>	20
<b>D1 (mm)</b>	35
<b>D2 (mm)</b>	30
<b>D3 (mm)</b>	24
<b>D4 (mm)</b>	9
<b>D5 (mm)</b>	9
<b>D6 (mm)</b>	0
<b>D7</b>	5
<b>E (mm)</b>	49.6
<b>EE</b>	G1/8
<b>E1 (mm)</b>	0
<b>KF (mm)</b>	6
<b>LA (mm)</b>	0
<b>PL (mm)</b>	7.6
<b>RT</b>	M6
<b>T1 (mm)</b>	2
<b>T2 (mm)</b>	2.5
<b>TG (mm)</b>	32.5
<b>L (mm)</b>	49.6

<b>ZA (mm)</b>	61.0
<b>ZB (mm)</b>	74.0
<b>L1 (mm)</b>	12.0
<b>L2 (mm)</b>	82.0
<b>L3 (mm)</b>	88
<b>L4 (mm)</b>	91
<b>R (mm)</b>	18
<b>P (mm)</b>	3.5
<b>B1 (mm)</b>	8
<b>SW1 (mm)</b>	17.5
<b>T3 (mm)</b>	2.0