

Stopper cylinders - Series ST

Product code: ST322R040A020

Datasheet creation date: 10/03/2025 00:17

Check the most updated document online [click here](#)



TECHNICAL DATA

Series	ST32
Operation	2=double-acting
Design	R = anti-rotation
Diameter (mm)	40
Construction	A = standard
Stroke (mm)	20

Stopper cylinders - Series ST

Product code: ST322R040A020

DIMENSIONS

AF (mm)	14.5
BG (mm)	0.0
G (mm)	14.3
H1 (mm)	0.0
D (mm)	25
D1 (mm)	43
D2 (mm)	35
D3 (mm)	29
D4 (mm)	12
D5 (mm)	12
D6 (mm)	0
D7	5
E (mm)	57.0
EE	G1/8
E1 (mm)	0
KF (mm)	8
LA (mm)	0
PL (mm)	7.6
RT	M6
T1 (mm)	2
T2 (mm)	2.5
TG (mm)	38.0
L (mm)	57.0

ZA (mm)	66.5
ZB (mm)	80.0
L1 (mm)	12.5
L2 (mm)	90.0
L3 (mm)	97
L4 (mm)	101
R (mm)	22
P (mm)	5.0
B1 (mm)	8
SW1 (mm)	22.0
T3 (mm)	2.5