

## Stopper cylinders - Series ST

Product code: ST324A032F025

Datasheet creation date: 10/03/2025 00:19

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |                             |
|----------------------|-----------------------------|
| <b>Series</b>        | ST32                        |
| <b>Operation</b>     | 4=single-acting rear spring |
| <b>Design</b>        | A = standard                |
| <b>Diameter (mm)</b> | 32                          |
| <b>Construction</b>  | F = female rod thread       |
| <b>Stroke (mm)</b>   | 25                          |

## Stopper cylinders - Series ST

Product code: ST324A032F025

### **DIMENSIONS**

|         |      |
|---------|------|
| AF (mm) | 11.0 |
| BG (mm) | 0.0  |
| G (mm)  | 14.3 |
| H1 (mm) | 0.0  |
| D (mm)  | 20   |
| D1 (mm) | 35   |
| D2 (mm) | 30   |
| D3 (mm) | 24   |
| D4 (mm) | 9    |
| D5 (mm) | 9    |
| D6 (mm) | 0    |
| D7      | 5    |
| E (mm)  | 49.6 |
| EE      | G1/8 |
| E1 (mm) | 0    |
| KF (mm) | 6    |
| LA (mm) | 0    |
| PL (mm) | 7.6  |
| RT      | M6   |
| T1 (mm) | 2    |
| T2 (mm) | 2.5  |
| TG (mm) | 32.5 |
| L (mm)  | 49.6 |

|          |      |
|----------|------|
| ZA (mm)  | 61.0 |
| ZB (mm)  | 74.0 |
| L1 (mm)  | 12.0 |
| L2 (mm)  | 82.0 |
| L3 (mm)  | 88   |
| L4 (mm)  | 91   |
| R (mm)   | 18   |
| P (mm)   | 3.5  |
| B1 (mm)  | 8    |
| SW1 (mm) | 17.5 |
| T3 (mm)  | 2.0  |