

Stopper cylinders - Series ST

Product code: ST329A040F020

Datasheet creation date: 10/03/2025 00:20

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|-----------------------------|
| Series | ST32 |
| Operation | 9=double-acting rear spring |
| Design | A = standard |
| Diameter (mm) | 40 |
| Construction | F = female rod thread |
| Stroke (mm) | 20 |

Stopper cylinders - Series ST

Product code: ST329A040F020

■ DIMENSIONS

| | |
|---------|------|
| AF (mm) | 14.5 |
| BG (mm) | 0.0 |
| G (mm) | 14.3 |
| H1 (mm) | 0.0 |
| D (mm) | 25 |
| D1 (mm) | 43 |
| D2 (mm) | 35 |
| D3 (mm) | 29 |
| D4 (mm) | 12 |
| D5 (mm) | 12 |
| D6 (mm) | 0 |
| D7 | 5 |
| E (mm) | 57.0 |
| EE | G1/8 |
| E1 (mm) | 0 |
| KF (mm) | 8 |
| LA (mm) | 0 |
| PL (mm) | 7.6 |
| RT | M6 |
| T1 (mm) | 2 |
| T2 (mm) | 2.5 |
| TG (mm) | 38.0 |
| L (mm) | 57.0 |

| | |
|----------|------|
| ZA (mm) | 66.5 |
| ZB (mm) | 80.0 |
| L1 (mm) | 12.5 |
| L2 (mm) | 90.0 |
| L3 (mm) | 97 |
| L4 (mm) | 101 |
| R (mm) | 22 |
| P (mm) | 5.0 |
| B1 (mm) | 8 |
| SW1 (mm) | 22.0 |
| T3 (mm) | 2.5 |