

Stopper cylinders - Series ST

Product code: ST329R020R015

Datasheet creation date: 10/03/2025 00:18

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|----------------------|-----------------------------|
| Series | ST32 |
| Operation | 9=double-acting rear spring |
| Design | R = anti-rotation |
| Diameter (mm) | 20 |
| Construction | R = with roller |
| Stroke (mm) | 15 |

Stopper cylinders - Series ST

Product code: ST329R020R015

■ DIMENSIONS

| | |
|----------------|------|
| AF (mm) | 6.0 |
| BG (mm) | 20.0 |
| G (mm) | 10.9 |
| H1 (mm) | 0.0 |
| D (mm) | 12 |
| D1 (mm) | 25 |
| D2 (mm) | 0 |
| D3 (mm) | 0 |
| D4 (mm) | 9 |
| D5 (mm) | 5 |
| D6 (mm) | 9 |
| D7 | 4 |
| E (mm) | 35.8 |
| EE | M5 |
| E1 (mm) | 0 |
| KF (mm) | 3 |
| LA (mm) | 5 |
| PL (mm) | 6.5 |
| RT | M5 |
| T1 (mm) | 0 |
| T2 (mm) | 2.5 |
| TG (mm) | 22.0 |
| L (mm) | 35.8 |

| | |
|-----------------|------|
| ZA (mm) | 53.5 |
| ZB (mm) | 64.0 |
| L1 (mm) | 9.5 |
| L2 (mm) | 68.0 |
| L3 (mm) | 71 |
| L4 (mm) | 73 |
| R (mm) | 10 |
| P (mm) | 2.0 |
| B1 (mm) | 4 |
| SW1 (mm) | 10.0 |
| T3 (mm) | 1.2 |