

## Stopper cylinders - Series ST

Product code: ST329R040R030

Datasheet creation date: 10/03/2025 00:18

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                      |                             |
|----------------------|-----------------------------|
| <b>Series</b>        | ST32                        |
| <b>Operation</b>     | 9=double-acting rear spring |
| <b>Design</b>        | R = anti-rotation           |
| <b>Diameter (mm)</b> | 40                          |
| <b>Construction</b>  | R = with roller             |
| <b>Stroke (mm)</b>   | 30                          |

## Stopper cylinders - Series ST

Product code: ST329R040R030

### DIMENSIONS

|         |      |
|---------|------|
| AF (mm) | 14.5 |
| BG (mm) | 0.0  |
| G (mm)  | 14.3 |
| H1 (mm) | 0.0  |
| D (mm)  | 25   |
| D1 (mm) | 43   |
| D2 (mm) | 35   |
| D3 (mm) | 29   |
| D4 (mm) | 12   |
| D5 (mm) | 12   |
| D6 (mm) | 0    |
| D7      | 5    |
| E (mm)  | 57.0 |
| EE      | G1/8 |
| E1 (mm) | 0    |
| KF (mm) | 8    |
| LA (mm) | 0    |
| PL (mm) | 7.6  |
| RT      | M6   |
| T1 (mm) | 2    |
| T2 (mm) | 2.5  |
| TG (mm) | 38.0 |
| L (mm)  | 57.0 |

|          |      |
|----------|------|
| ZA (mm)  | 66.5 |
| ZB (mm)  | 80.0 |
| L1 (mm)  | 12.5 |
| L2 (mm)  | 90.0 |
| L3 (mm)  | 97   |
| L4 (mm)  | 101  |
| R (mm)   | 22   |
| P (mm)   | 5.0  |
| B1 (mm)  | 8    |
| SW1 (mm) | 22.0 |
| T3 (mm)  | 2.5  |