

Direct operated solenoid valves - Series W

Product code: W000-305-F13

Datasheet creation date: 20/05/2026 06:48

Check the most updated document online [click here](#)




TECHNICAL DATA

Series	W
Body execution	0 = interface
Number of seats	00 = ISO 15218 interface
Number of ways - Functions	3 = 3/2 way - NC
Valve connections	0 = ISO 15218 interface
Orifice diameter	5 = Ø 1.1 mm
Materials	F = PBT body - FKM seals
Electrical connection	1 = cables 300 mm
Voltage - Absorbed power	3 = 24 V DC - 2 W
Fixing	= fixing screws for metal
Use with oxygen	= Not suitable for use with oxygen

Direct operated solenoid valves - Series W

Product code: W000-305-F13



DIMENSIONS

Series	W
Body execution	0 = interface
Number of seats	00 = ISO 15218 interface
Number of ways - Functions	3 = 3/2 way - NC
Valve connections	0 = ISO 15218 interface
Orifice diameter	5 = Ø 1.1 mm
Materials	F = PBT body - FKM seals
Electrical connection	1 = cables 300 mm
Voltage - Absorbed power	3 = 24 V DC - 2 W
Fixing	= fixing screws for metal
Use with oxygen	= Not suitable for use with oxygen