

## 28 系列流量控制阀

双向

接口 G1/8, G1/4, G3/8, G1/2




**28 系列流量控制阀**是一种双向流量控制阀，阀体由黄铜制成，表面镀镍，丁腈橡胶密封件和工程塑料旋钮。阀体进出接口为外螺纹或内螺纹，其螺纹规格有 G1/8, G1/4, G3/8 和 G1/2 四种，各具不同的公称流量。阀的连接管可采用尼龙管，也可以采用紫铜管。该系列阀适用于调节压缩空气、水或矿物油的流量。


### 综合参数

结构形式	针形
材料	黄铜阀体（表面镀镍），工程塑料旋钮，丁腈橡胶密封件
接口	G1/8 - G1/4 - G3/8 - G1/2
安装位置	任意
工作温度	0 ÷ 80°C（干燥空气 - 20°C）
工作压力	0 ÷ 10 bar
公称流量	见后续各尺寸表


### 2810... 型流量控制阀




尺寸表							
型号	A	L	T	Z	SW2	公称流量 (Nl/min)	自由流量 (l/min)
2810 1/8	G1/8	40	37	42.5	19	415	590
2810 1/4	G1/4	42	37	42.5	19	508	740
2810 3/8	G3/8	42	37	42.5	19	620	900
2810 1/2	G1/2	54	42	48	22	1540	2080




### 2820... 型流量控制阀




尺寸表								
型号	A	B	L	T	Z	SW2	公称流量 (Nl/min)	自由流量 (l/min)
2820 1/8	G1/8	G1/8	41	37	42.5	19	400	640
2820 1/4	G1/4	G1/4	44	37	42.5	19	530	840
2820 3/8	G3/8	G3/8	55.5	41.5	48	22	1415	1990
2820 1/2	G1/2	G1/2	59	42	49	22	1520	2150





### 2830... 型流量控制阀



尺寸表							
型号	B	L	T	Z	SW2	公称流量 (Nl/min)	自由流量 (l/min)
2830 1/8	G1/8	42	37	42.5	19	415	635
2830 1/4	G1/4	46	37	42.5	19	530	850
2830 3/8	G3/8	62	41.4	48	22	1415	1980
2830 1/2	G1/2	64	42	49	22	1520	2100




### 2819... 型流量控制阀





尺寸表										
型号	A	L	P	S	T	Z	S <sub>max</sub>	SW2	SW3	
2819 1/8	G1/8	40	1/4	23	47	52.5	7	19	17	
2819 1/4	G1/4	42	1/4	23	47	52.5	7	19	17	

### 2829... 型流量控制阀



尺寸表										
型号	A	B	L	P	S	T	Z	S <sub>max</sub>	SW2	SW3
2829 1/8	G1/8	G1/8	41	1/4	23	47	52.5	7	19	17
2829 1/4	G1/4	G1/4	44	1/4	23	47	52.5	7	19	17

### 2839... 型流量控制阀



尺寸表										
型号	A	L	P	S	T	Z	S <sub>max</sub>	SW2	SW3	
2839 1/8	G1/8	42	1/4	23	47	52.5	7	19	17	
2839 1/4	G1/4	46	1/4	23	47	52.5	7	19	17	
2839 3/8	G3/8	62	14X1	28	56.5	63	7	22	17	
2839 1/2	G1/2	64	14X1	29	57	64	7	22	17	