

Series CP directly operated and pressure compensated proportional solenoid valves

Function: 2/2-way NC Sizes: 16 and 20 mm



- » High flow and great precision
- » Low hysteresis
- » Cartridge body
- Pressure compensated version (size 20mm only) available
- » Suitable to work also with oxygen

Series CP directly operated proportional solenoid valves can be used where an open loop flow control is required, with gas mixtures or to control flows. Their cartridge design makes them particularly compact, thus they can be mounted directly near the workstation.

Series CP valves have been designed to optimize dimensions and reduce friction and stick-slip effects. The output flow is proportional to the control signal. Apart from the pressure compensated version, these valves can work also in vacuum. A minimum working pressure is thus not required.

GENERAL DATA

TECHNICAL FEATURES	Size 16mm, 2/2 NC	Size 20mm, 2/2 NC	Size 20mm, 2/2 NC pressure compensated
Operation Pneumatic connections Nominal diameters Free flow capacity Operating pressure Max overpressure Linearity (5-95%) Hysteresis Repeatibility Operating temperature Media	proportional directly operated cartridge 1 mm - 1.5 mm - 2 mm 70 Nl/min - 80 Nl/min - 90 Nl/min 3 bar - 5 bar - 8 bar 16 bar 3% FS 10% FS 5% FS 10% C ÷ 50°C filtered compressed air, unlubricated, according to ISO 8573-1 class 7.4.4, inert gas.	proportional directly operated cartridge 3 mm - 3.5 mm 145 Nl/min - 165 Nl/min 2.8 bar - 2 bar 16 bar 5% FS 15% FS 15% FS 10°C ÷ 50°C filtered compressed air, unlubricated, according to ISO 8573-1 class 7.4.4, inert gas.	proportional pressure compensated cartridge 4.4 mm 200 l/min 2.8 bar (max pressure 6 bar) 16 bar 2% FS 15% FS 5% FS 10°C ÷ 50°C filtered compressed air, unlubricated, according to ISO 8573-1 class 7.4.4, inert gas.
Installation	in any position	in any position	in any position
MATERIALS IN CONTACT WITH THE MEDIUM			
Body Seals	brass, stainless steel, PPS FKM	brass, stainless steel, PPS FKM	brass, stainless steel, PPS FKM
ELECTRICAL FEATURES			
Operation Operation voltage Max power consumption Nominal resistance Rated current Duty cycle Electrical connection Protection class Average lifecycles	PWM > 1000 Hz or current control 6 V DC, 12 V DC, 24 V DC 3.1 W 11.8 Ohm - 37.6 Ohm - 184.7 Ohm 410 mA, 238 mA, 103 mA 100% with air flow cable 300mm AWG24 IP00 / IP40 50000000	PWM > 500 Hz or current control 6 V DC, 12 V DC, 24 V DC 5 W, 3.7 W 5.4 Ohm, 21.6 Ohm, 86.4 Ohm, 6.4 Ohm, 25.1 Ohm, 102.1 Ohm 820 mA, 410 mA, 205 mA 100% with air flow cable 300mm AWG24 IP00 / IP40 50000000	PWM > 1000 Hz or current control 6 V DC, 12 V DC, 24 V DC 4.2 W 6.4 Ohm, 25.1 Ohm, 102.1 Ohm 700 mA, 350 mA, 175 mA 100% with air flow cable 300mm AWG24 IP00 / IP40 50000000
Command signal	recommended PWM: 1000 Hz	recommended PWM: 500 Hz	recommended PWM: 1000 Hz

Versions available on demand base with 1/8, 1/4 ports

CODING EXAMPLE


СР	- C 6 2	1 - G N	N 2 - 0 P 3					
CD	SERIES							
СР								
C	PORTS: C = cartridge S = subbase							
6	BODY SIZE: 6 = size 16mm 7 = size 20mm 9 = size 20mm pressure compensated							
2	NUMBER OF PORTS: 2 = 2-way							
1	FUNCTION: 1 = NC							
G	ORIFICE DIAMETRES: F = 1mm (size 16mm only) G = 1.5mm (size 16mm only) N = 2mm (size 16mm only)	M = 3mm (size 20mm only) P = 3.5mm (size 20mm only)	T = ø 4.4 mm (size 20mm only, pressure compensated)					
W	SEAL MATERIAL: W = FKM							
2	BODY MATERIAL: 2 = BRASS							
0	OVERMOULDING MATERIAL OF COIL: 0 = cartridge							
Ρ	COIL DIMENSIONS: P = ø 16 7 = ø 20							
3	VOLTAGE: 1 = 6 V DC 3.1 W (size 16mm only) 3 = 24 V DC 3.1 W (size 16mm only) 5 = 12 V DC 3.1 W (size 16mm only)	10 = 6 V DC 4.2 W (size 20mm only, pressure compensated) 11 = 24 V DC 4.2 W (size 20mm only, pressure compensated) 12 = 12 V DC 4.2 W (size 20mm only, pressure compensated)						

HYSTERESIS AND RESPONSE TIMES

DIAGRAM LEGEND:

Q = flow (l/min) I = current (A) FS = full scale


NOTE TO THE TABLE: * in the pressure compensated version the counter pressure at the value outlet must be always lower than 15-20% of the inlet pressure.



RESPONSE TIMES calculated according to the maximum flow at each operating pressure. [Electromechanical response time: 10 ms]

REST ON SETTINES	concorrence according to the maxima	in non at each oper	dung press		and medit esponse anner 20 m			
ø	Inlet pressure (bar)	Load	response tii	me (ms)	Exhaus	t response tir	ne (ms)	
		0% - 10%	0% - 90%	10% - 90%	100% - 90%	100% - 10%	90% - 10%	
1 mm	8	12	42	30	9	33	24	
1.5 mm	5	12	39	27	9	33	24	
2 mm	3	11	39	28	9	33	26	
3 mm	2.8	13	29	16	14	28.5	14.5	
3.5 mm	2	15	31	16	12.5	27.5	15	
4.4 mm *	2.8	13	52	49	10	37	27	


FLOW DIAGRAMS - Size 16mm



Nominal diameter 1mm

Q = flow (l/min) I = current (A) P1 = pressure in load (bar) P2 = 0 [free flow pressure] (bar) Nominal diameter 1.5mm

Q = flow (l/min) I = current (A) P1 = pressure in load (bar) P2 = 0 [free flow pressure] (bar)



Nominal diameter 2mm


Q = flow (l/min)


I = current(A)

P1 = pressure in load (bar)

P2 = 0 [free flow pressure] (bar)

FLOW DIAGRAMS - Size 20mm





Nominal diameter 3mm

Q = flow (l/min) I = current (A) P1 = pressure in load (bar) P2 = 0 [free flow pressure] (bar) Nominal diameter 3.5mm

Q = flow (l/min) I = current (A) P1 = pressure in load (bar) P2 = 0 [free flow pressure] (bar)

Q (NI/min) 300 P2=0 bar P1=6 bar P1=5 bar 250 P1=4 bar P1=3 bar P1=2.8 bar 200 P1=2 bar 150 P1=1 bar 100 50 0 0 20 40 60 80 100 FS I (%)


FLOW DIAGRAMS - Size 20mm pressure compensated

Nominal diameter 4.4mm

Q = flow (l/min) I = current (A) P1 = pressure in load (bar) P2 = 0 [free flow pressure] (bar) FS = full scale

Automation


MAXIMUM FLOW ACCORDING TO THE INLET PRESSURE



P = Inlet pressure (bar)

Q = Flow (Nl/min) P = Inlet pressure (bar)


MAXIMUM FLOW ACCORDING TO THE INLET PRESSURE



Size 20mm pressure compensated

Q = Flow (Nl/min)


P = Inlet pressure (bar)



VES
VAL
2
E
S
M
\Box
RT
DPO
PRO
9
ES
SER


Mod.	Orifice Ø (mm)	Max operating pressure (bar)	Max flow (Nl/min)	Max flow kv (l/min)	Operation voltage (V DC)	Max current (mA)
CP-C621-FW2-0P1	1	8	70	0.55	6	410
CP-C621-GW2-0P1	1.5	5	80	0.88	6	410
CP-C621-NW2-OP1	2	3	90	1.42	6	410
CP-C621-FW2-0P3	1	8	70	0.55	24	103
CP-C621-GW2-0P3	1.5	5	80	0.88	24	103
CP-C621-NW2-OP3	2	3	90	1.42	24	103
CP-C621-FW2-0P5	1	8	70	0.55	12	238
CP-C621-GW2-0P5	1.5	5	80	0.88	12	238
CP-C621-NW2-0P5	2	3	90	1.42	12	238

Solenoid valves, size 16m




Mod.	Orifice Ø (mm)	Max operating pressure (bar)	Max flow (Nl/min)	Max flow kv (l/min)	Operation voltage (V DC)	Max current (mA)
CPN-C621-FW2-0P1	1	8	70	0.55	6	410
CPN-C621-GW2-0P1	1.5	5	80	0.88	6	410
CPN-C621-NW2-OP1	2	3	90	1.42	6	410
CPN-C621-FW2-0P3	1	8	70	0.55	24	103
CPN-C621-GW2-0P3	1.5	5	80	0.88	24	103
CPN-C621-NW2-OP3	2	3	90	1.42	24	103
CPN-C621-FW2-0P5	1	8	70	0.55	12	238
CPN-C621-GW2-0P5	1.5	5	80	0.88	12	238
CPN-C621-NW2-0P5	2	3	90	1.42	12	238

Solenoid valves, size 20mm



Mod.	Orifice Ø (mm)	Max operating pressure (bar)	Max flow (Nl/min)	Max flow kv (l/min)	Operation voltage (V DC)	Max current (mA)
CP-C721-MW2-072	3	2.8	150	2.8	12	313
CP-C721-MW2-074	3	2.8	150	2.8	24	154
CP-C721-MW2-076	3	2.8	150	2.8	6	615
CP-C721-PW2-072	3.5	2	130	3	12	313
CP-C721-PW2-074	3.5	2	130	3	24	154
CP-C721-PW2-076	3.5	2	130	3	6	615
CP-C721-PW2-077	3.5	2	180	4.5	6	820
CP-C721-PW2-078	3.5	2	180	4.5	12	410
CP-C721-PW2-079	3.5	2	180	4.5	24	205

Solenoid valves, size 20mm pressure compensated




Mod.	Orifice Ø (mm) Max operating pressure (bar)		Max flow (Nl/min)	Max flow (Nl/min) Max flow kv (l/min)		Max current (mA)
CP-C921-TW2-0710	4.4	6	200	4	6	700
CP-C921-TW2-0711	4.4	6	200	4	24	175
CP-C921-TW2-0712	4.4	6	200	4	12	350

Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com New


Sub-base







т



Φ

¢

E±0.1

<u>M3</u>



Mod.	Ø	А	В	С	D	E	G	Н	L	L1
CP-S6	16	20.7	7.5	14.2	19.5	12	G1/8	27	32	16
CP-S7	20	25.2	8	14	22.5	15	G1/4	31.5	45	22