# Series CFB stainless steel solenoid valves

2/2-way - Normally Closed (NC) 3/2-way - Normally Closed (NC)



Series CFB Stainless Steel direct acting solenoid valves for general purpose, 2/2-way and 3/2-way NC, are the ideal solution for a wide range of applications whereby the environment and fluids used can be particularly aggressive and contaminating. Special versions are available on demand.

- » Stainless steel version for particularly aggressive environment and fluids
- » High reliability over time, even in hard working conditions
- » Compact dimensions
- » Suitable to control inert and medical gases, alimentary fluids and beverages

The valve function is determined by a poppet and the operation is direct. Different versions are available according to the nominal diameter and to the threaded ports, as shown in the following tables. They can thus satisfy various requirements in terms of flow rates and working pressures.

#### **GENERAL DATA**

TECHNICAL FEATURES	
Function Operation Pneumatic connections Orifice diameter Flow coefficient Kv (m <sup>3</sup> /h) Operating pressure Operating temperature Media Response time	2/2 NC - 3/2 NC direct acting poppet type G1/8 G1/2 threads 1.5 4 mm 0.08 0.28 0 ÷ 4 25 bar -10 ÷ 140 °C air, water, liquid and gaseous fluids with max viscosity 37 cSt (5° E) ON <15 ms - OFF <25 ms
Installation	in any position
MATERIALS IN CONTACT WITH THE MEDIUM	
Body Seals Internal parts	stainless steel 316L FKM - EPDM stainless steel
ELECTRICAL FEATURES	
Voltage Voltage tolerance Power consumption Duty cycle Insulation class Electrical connection Protection class	12 V DC, 24 V DC - 24V AC 50 Hz, 110 V AC 50/60 Hz, 220/230 V AC 50/60 Hz ±5% (DC) - ±10% (AC) 19 W (DC) - 15 VA (AC) ED 100% H (180°C) DIN EN 175-301-803-A connector IP65 with connector
Special versions available on demand	

It is recommended to use connections with internal diameters bigger than valve orifices, otherwise there may be a performance change.

SERIES CFB STAINLESS STEEL SOLENOID VALVES

#### CODING EXAMPLE

1		1									I		
CFB	-	D		2	1	Α	-	W	Χ	-		38	E
	-												
CFB	SERIES												
D	OPERATION D = direct												
2	NUMBER OF V 2 = 2/2-way 3 = 3/2-way	- NC	IONS										
1	CONNECTION 1 = G1/8 2 = G1/4 3 = G3/8 4 = G1/2	S											
A	ORIFICE DIAM A = 1.5 mm B = 2 mm C = 2.5 mm E = 3 mm F = 4 mm	IETER											
W	SEALS MATER W = FKM E = EPDM	IAL											
X	BODY MATERI X = 316L stair												
<b>B8</b>	SOLENOID DI B8 = 30 mm	MENSION											
E	VOLTAGE - PO B = 24 V 50/6 D = 110 V 50/ E = 230 V 50/ 2 = 12 V DC - 3 = 24 V DC -	50 Hz - 15 VA /60 Hz - 15 V /60 Hz - 15 V 19 W	A										

## TABLE FOR THE COUPLING BETWEEN SOLENOIDS AND VALVES

For solenoids and their connectors see the dedicated section. Coil mod. B8... - DIN EN 175 301-803-A = connector mod. 124-...

\* = complete the code according to coding example

Mod.	24V AC 50 Hz	110V AC 50/60 Hz	220/230V AC 50/60 Hz	12V DC	24V DC
CFB-D21A-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D21B*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D21C-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D22B-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D22C-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D22E-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D23E-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D23F-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D24E-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D24F-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D32A-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D32B-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D32C-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)
CFB-D32E-*	B8B (15VA)	B8D (15VA)	B8E (15VA)	B82 (19W)	B83 (19W)


### Series CFB solenoid valve - direct acting - 2/2 and 3/2 NC




The direct control of these solenoid valves allows to operate with working pressures that are equal to zero.

Ports: from G1/8 to G1/2.

\* add - SEALS MATERIAL - VOLTAGE (see CODING EXAMPLE)






٠

ø

Nh

7



Mod.	Function	Connections	Orifice Ø (mm)	Kv (m³/h)	Pressure min-max (bar)	А	В	С	D	F	G	Н	Ι	Pneumatic symbol
CFB-D21AX-*	2/2 NC	G1/8	1.5	0.08	0 ÷ 25	71.7	59.2	21	42	15	8	25	29	EV01
CFB-D21BX-*	2/2 NC	G1/8	2	0.10	0 ÷ 22	71.7	59.2	21	42	15	8	25	29	EV01
CFB-D21CX-*	2/2 NC	G1/8	2.5	0.14	0÷15	71.7	59.2	21	42	15	8	25	29	EV01
CFB-D22BX-*	2/2 NC	G1/4	2	0.10	0 ÷ 22	71.7	59.2	21	42	18	8	25	28	EV01
CFB-D22CX-*	2/2 NC	G1/4	2.5	0.14	0÷15	71.7	59.2	21	42	18	8	25	28	EV01
CFB-D22EX-*	2/2 NC	G1/4	3	0.18	0÷10	71.7	59.2	21	42	18	8	25	28	EV01
CFB-D23EX-*	2/2 NC	G3/8	3	0.18	0÷10	71.7	59.2	22.5	45	23	9.5	25	28	EV01
CFB-D23FX-*	2/2 NC	G3/8	4	0.28	0 ÷ 6	71.7	59.2	22.5	45	23	9.5	25	28	EV01
CFB-D24EX-*	2/2 NC	G1/2	3	0.18	0÷10	76.7	61.7	24.5	49	27.5	11	30	31	EV01
CFB-D24FX-*	2/2 NC	G1/2	4	0.28	0 ÷ 6	76.7	61.7	24.5	49	27.5	11	30	31	EV01
CFB-D32AX-*	3/2 NC	G1/4	1.5	0.08	0÷13	77.8	65.3	21	42	18	8	25	28	EV45
CFB-D32BX-*	3/2 NC	G1/4	2	0.1	0÷9	77.8	65.3	21	42	18	8	25	28	EV45
CFB-D32CX-*	3/2 NC	G1/4	2.5	0.14	0÷5.5	77.8	65.3	21	42	18	8	25	28	EV45
CFB-D32EX-*	3/2 NC	G1/4	3	0.18	0÷4	77.8	65.3	21	42	18	8	25	28	EV45