


Valves and solenoid valves Series 4

New models

3/2, 5/2 and 5/3-way CC, CO Ports: G1/8, G1/4, G3/8, G1/2



Series 4 solenoid valves have been designed in the 3/2, 5/2, 5/3 versions and with the following two devices of actuation:

- electropneumatically actuated with mechanical spring return
- electropneumatically actuated and return with external and internal air pressure supply

Series 4 valves are equipped with a manual override which allows a stable operation and they are particularly suitable for mounting in arduous conditions.

All these valves can be operated by solenoids Series U, G A8 and H8.

Pneumatically actuated valves 3/2 NC become NO when the supply is on connection 3.

- » The different ports allow flows from 650 to 4000 Nl/min
- » New models available: with G3/8 ports and 1800 Nl/min flow

GENERAL DATA

Construction balanced spool type

Valve functions 3/2 - 5/2 - 5/3-way CC, CO

Materials AL body and subbases stainless steel spool technopolymer end cover NBR PU seals

Ports G1/8 - G1/4 - G3/8 - G1/2

Installation in any position

Operating pressure see table

Medium filtered air, without lubrication. If lubricated air is used, it is recommended to use ISOVG32 oil.

Once applied the lubrication should never be interrupted.

2.15.03

C⊀ CAMOZZI




CODING EXAMPLE


4	5	4	-	015	-	22	IL	-	U7	7
4	SERIES									
5	NUMBER (3 = 3/2 NO 4 = 3/2 NO 5 = 5/2 6 = 5/3 CO 7 = 5/3 CO		DNS:							
4	PORTS: 2C = G1/2 2N = G1/2 3 = G3/8 4 = G1/4 8 = G1/8	(high flow)								
015										
22	22 = mech	INTERFACE:: n. sol. 22 x 22 n. sol. 32 x 32 (or	nly for 452C versi	on)						
IL	TYPE OF MANUAL OVERRIDE: = bistable, standard IL = bistable, lever type (available on demand) IM = monostable (available on demand)									
U7	A6 = PPS / A8 = PPS / G7 = PA / 3 G8 = PA / 3 G9 = PA / 3	32 x 32 (only for 30 x 30 22 x 22 30 x 30 (24 V DC of 22 x 58 V0 / 30 x 30		NSIONS:						


TYPES OF MANUAL OVERRIDE

7



SOLENOID VOLTAGE (see the dedicated section 2.35)






Example of solenoid monostable valve (IM) and bistable valve with a lever type manual override (IL).




3/2-way solenoid valve G1/8, monostable - Mod. 438... and 448...



These solenoid valves, which have electropneumatic actuation and spring return, are available in the NC (closed) or NO (open) version.






Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
438-015-22	3/2 NC	650	2.5 ÷ 10	EV10
438-016-22	3/2 NC	650	2.5 ÷ 10	EV16
448-015-22	3/2 NO	650	2.5 ÷ 10	EV12
448-016-22	3/2 NO	650	2.5 ÷ 10	EV17

3/2-way solenoid valve G1/8, bistable - Mod. 438-011...



These solenoid valves, which have electropneumatic actuation and return, assume the NC (closed) or NO (open) operating status depending on the last pulse received.



	2	EV14
12	1	3 10


Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	
438-011-22	3/2	650	2 ÷ 10	




5/2-way solenoid valves, G1/8, monostable - Mod 458...



These solenoid valves, which have electropneumatic actuation and spring return, are suitable for operating double-acting cylinders.






Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
458-015-22	5/2	650	2.5 ÷ 10	EV18
458-016-22	5/2	650	2.5 ÷ 10	EV20
458-015-22IL	5/2	650	2.5 ÷ 10	EV18

5/2-way solenoid valves, G1/8, bistable - Mod 458-011...



These solenoid valves, with electropneumatic actuation and return, are suitable for operating double-acting cylinders.



		4	l		2	EV23
	T_	Ų,	,	Ź	}	Æ.
1/		-	1	П	5	12

Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)
458-011-22	5/2	650	2 ÷ 10




5/3-way solenoid valve, G1/8 - Mod. 468-011... and 478-011...



CC = Centres Closed CO = Centres Open






Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
468-011-22	5/3 CC	600	2.5 ÷ 10	EV28
478-011-22	5/3 CO	600	2.5 ÷ 10	EV32

3/2-way solenoid valve, G1/4, monostable Mod. 434 and Mod. 444



These solenoid valves, which have electropneumatic actuation and spring return, are available in the NC (closed) or NO (open) version.



	2	EV10		2	EV16		2	EV12		2	EV17
	TIT	w		1 7 7	b		Ţ.	J.w	Ä	<u>, , </u>	H
12	1	3	12	1	3	10	1	3	10	1	3


Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
434-015-22	3/2 NC	1250	2.5 ÷ 10	EV10
434-016-22	3/2 NC	1250	2.5 ÷ 10	EV16
444-015-22	3/2 NO	1250	2.5 ÷ 10	EV12
444-016-22	3/2 NO	1250	2.5 ÷ 10	EV17
434-015-22IL	3/2 NC	1250	2.5 ÷ 10	EV10


€ CAMOZZI

3/2-way solenoid valve, G1/4, bistable - Mod. 434-011...



These solenoid valves, which have electropneumatic actuation and return, assume the NC (closed) or NO (open) position depending on the last pulse received.







Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)
434-011-22	3/2	1250	2 ÷ 10


5/2-way solenoid valve, G1/4, monostable - Mod. 454...



These solenoid valves, which have electropneumatic actuation and spring return, are suitable for operating double-acting cylinders.











Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
454-015-22	5/2	1250	2.5 ÷ 10	EV18
454-016-22	5/2	1250	2.5 ÷ 10	EV20

5/2-way solenoid valve, G1/4, bistable - Mod. 454-011...



These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.






Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)
454-011-22	5/2	1250	2 ÷ 10
454-011-22IL	5/2	1250	2 ÷ 10


5/2-way solenoid valve, G1/4, monostable - Mod. 454-V...



These solenoid valves, which have electropneumatic actuation and spring or pneumatic spring return are suitable for operating double-acting cylinders.









Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
454-V15-22	5/2	1250	2.5 ÷ 10	EV18
454-V16-22	5/2	1250	2.5 ÷ 10	EV20

5/2-way solenoid valve, G1/4, bistable - Mod. 454-V11...



These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.





Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)
454-V11-22	5/2	1250	2 ÷ 10


5/3-way solenoid valve, G1/4 - Mod. 464-011... e 474-011...



CC = Centres Closed

CO = Centres Open





Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol
464-011-22	5/3 CC	1250	2.5 ÷ 10	EV28
474-011-22	5/3 CO	1250	2.5 ÷ 10	EV32


CAMOZZI Automation


3/2-way solenoid valve, G3/8, monostable Mod. 433... and Mod. 443...

New



These solenoid valves, which have electropneumatic actuation and spring return, are available in the NC (closed) or NO (open) version.
The E15 version can work both NC and NO.






Mod.	Function	Flow Qn (Nl/min)	Working pressure (bar)	Min. pilot pressure (bar)	Symbol
433-015-22	3/2 NC	1800	2.5 ÷ 10	-	EV10
433-E15-22	3/2	1800	-0.9 ÷ 10	2.5	EV11
433-016-22	3/2 NC	1800	2.5 ÷ 10	-	EV16
443-015-22	3/2 NO	1800	2.5 ÷ 10	-	EV12
443-016-22	3/2 NO	1800	2.5 ÷ 10	-	EV17


3/2-way solenoid valve, G3/8, bistable - Mod. 433...

New



These solenoid valves, which have electropneumatic actuation and return, assume the NC (closed) or NO (open) position depending on the last pulse received.
The E11 version can work both NC and NO.






Mod.	Function	Flow Qn (Nl/min)	Working pressure (bar)	Min. pilot pressure (bar)	Symbol
433-011-22	3/2	1800	2 ÷ 10	-	EV14
433-E11-22	3/2	1800	-0.9 ÷ 10	2	EV15

New

5/2-way solenoid valve, G3/8, monostable - Mod. 453...



These solenoid valves, which have electropneumatic actuation and spring return, are suitable for operating double-acting cylinders.



EV18	
	4 2
	JI /Tww
14	5 11 13



	EV20			
	1 -	4	1	2
			\Box /	
14 5 1 1 3	14	<u> </u>	11	F


Mod.	Function	Flow Qn (Nl/min)	Working pressure (bar)	Min. pilot pressure (bar)	Symbol
453-015-22	5/2	1800	2.5 ÷ 10	-	EV18
453-E15-22	5/2	1800	-0.9 ÷ 10	2.5	EV19
453-016-22	5/2	1800	2.5 ÷ 10	-	EV20

5/2-way solenoid valve, G3/8, bistable - Mod. 453...





These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.







Mod.	Function	Flow Qn (Nl/min)	Working pressure (bar)	Min. pilot pressure (bar)	Symbol
453-011-22	5/2	1800	2 ÷ 10	-	EV23
453-E11-22	5/2	1800	-0.9 ÷ 10	2	EV25


C CAMOZZI


5/3-way solenoid valve, G3/8 - Mod. 463-... and 473-...





CC = Centres Closed CO = Centres Open






Mod.	Function	Flow Qn (Nl/min)	Working pressure (bar)	Min. pilot pressure (bar)	Symbol
463-011-22	5/3 CC	1600	2.5 ÷ 10	-	EV28
463-E11-22	5/3 CC	1600	-0.9 ÷ 10	2.5	EV29
473-011-22	5/3 CO	1600	2.5 ÷ 10	-	EV32
473-E11-22	5/3 CO	1600	-0.9 ÷ 10	2.5	EV34

5/2-way solenoid valve, G1/2, monostable - Mod. 452C...



These solenoid valves, which have electropneumatic actuation and spring or pneumatic spring return are suitable for operating doubleacting cylinders.



	4 2 EV	18 4 2 EI	V20
	TIV /TW		
14	5 11 13	14 5 1 3	


Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	Symbol	
452C-015-50-A6*	5/2	2500	2.5 ÷ 10	EV18	* choose the desired voltage
452C-016-50-A6*	5/2	2500	2.5 ÷ 10	EV20	* choose the desired voltage
452C-015	5/2	2500	2.5 ÷ 10		* choose the desired voltage
452C-015-22	5/2	2500	2.5 ÷ 10		* choose the desired voltage
452C-016	5/2	2500	2.5 ÷ 10		* choose the desired voltage




5/2-way solenoid valve, G1/2, bistable - Mod. 452C-011...



These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.






Mod.	Function	Flow rate Qn (Nl/min)	Operating pressure (bar)	
452C-011-50-A6*	5/2	2500	2 ÷ 10	* choose the desired voltage
452C-011-22	5/2	2500	2 ÷ 10	* choose the desired voltage
452C-011	5/2	2500	2 ÷ 10	* choose the desired voltage


5/2-way solenoid valve, G1/2, monostable - Mod. 452N-...





These solenoid valves, which have electropneumatic actuation and spring or pneumatic spring return are suitable for operating doubleacting cylinders.






Mod.	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
452N-015-22	5/2	4000	-	2.5 ÷ 10	EV18
452N-016-22	5/2	4000	-	2.5 ÷ 10	EV20
452N-E15-22	5/2	4000	2.5	-0.9 ÷ 10	EV19


5/2-way solenoid valve, G1/2, bistable - Mod. 452N-...



These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.









Mod.	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
452N-011-22	5/2	4000	-	2 ÷ 10	EV23
452N-E11-22	5/2	4000	2	-0.9 ÷ 10	EV25

5/3-way solenoid valve, G1/2, bistable - Mod. 462N-..., 472N-...



These solenoid valves, which have electropneumatic actuation and return, are suitable for operating double-acting cylinders.







Mod.	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
462N-011-22	5/3 CC	3300	-	2.5 ÷ 10	EV28
462N-E11-22	5/3 CC	3300	2.5	-0.9 ÷ 10	EV29
472N-011-22	5/3 CO	3300	-	2.5 ÷ 10	EV32
472N-E11-22	5/3 CO	3300	2.5	-0.9 ÷ 10	EV34

3/2-way valve, G1/8 port, monostable Mod. 438-35








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
438-35	in-line/on manifold	3/2 NC	700	2.5	-0.9 ÷ 10

5/2-way valve, G1/8 port, monostable Mod. 458-35








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
458-35	in-line/manifold	5/2	700	2.5	-0.9 ÷ 10

3/2-way valve, G1/8 port, bistable Mod. 438




These valves can work NC or NO according to the last pilot signal.




Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
438-33	in-line/on manifold	3/2	700	2	-0.9 ÷ 10	VP02
438-34	in-line/on manifold	3/2	700	2	-0.9 ÷ 10	VP03

5/2-way valve, G1/8 port, bistable Mod. 458








	4	2 <i>VP05</i>
<u></u>	1	1 3 12
14	5	1 13 12


Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
458-33	in-line/on manifold	5/2	700	2	-0.9 ÷ 10	VP06
458-34	in-line/on manifold	5/2	700	2	-0.9 ÷ 10	VP05

3/2-way valve, G1/4 port, monostable Mod. 434-35



This valve can work NC or NO depending on where the power supply is connected.






Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)
434-35	in-line/on manifold	3/2 NC	1250	2.5	-0.9 ÷ 10

5/2-way valve, G1/4 port, monostable Mod. 454-35








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
454-35	in-line/on manifold	5/2	1250	2.5	-0.9 ÷ 10

3/2-way valve, G1/4 port, bistable Mod. 434




These valves can work NC or NO according to the last pilot signal.




Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
434-33	in-line/on manifold	3/2 NC	1250	2	-0.9 ÷ 10	VP02
434-34	in-line/on manifold	3/2 NC	1250	2	-0.9 ÷ 10	VP03

5/2-way valve, G1/4 port, bistable Mod. 454









Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
454-33	in-line/on manifold	5/2	1250	2	-0.9 ÷ 10	VP06
454-34	in-line/on manifold	5/2	1250	2	-0.9 ÷ 10	VP05

5/3-way C.C. valve, G1/8, monostable, with central stable position



CC = Centres Closed






Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)
468-33	in-line/on manifold	5/3 CC	700	2.5	-0.9 ÷ 10


5/3-way CC CO valve, G1/4, monostable, central stable position



CC = Centres Closed








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
464-33	in-line/on manifold	5/3 CC	1250	2.5	-0.9 ÷ 10	VP08
474-33	in-line/on manifold	5/3 CO	1200	2.5	-0.9 ÷ 10	VP09

3/2-way valve, G3/8 port, monostable Mod. 433-35


New




This valve can work NC or NO depending on where the power supply is connected.











Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)
433-35	in-line/on manifold	3/2 NC	1800	2.5	-0.9 ÷ 10


5/2-way valve, G3/8 port, monostable Mod. 453-35

New









	4	2 VP04
	1	1 T ₃ W
14	5	11 13


Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
453-35	in-line/on manifold	5/2	1800	2.5	-0.9 ÷ 10


3/2-way valve, G3/8 port, bistable Mod. 433





These valves can work NC or NO according to the last pilot signal.













Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
433-33	in-line/on manifold	3/2 NC	1800	2	-0.9 ÷ 10	VP02
433-34	in-line/on manifold	3/2 NC	1800	2	-0.9 ÷ 10	VP03


5/2-way valve, G3/8 port, bistable Mod. 453












	4	12	VP06
14	5	113	-<1 <u>12</u>

Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
453-33	in-line/on manifold	5/2	1800	2	-0.9 ÷ 10	VP06
453-34	in-line/on manifold	5/2	1800	2	-0.9 ÷ 10	VP05


5/3-way CC CO valve, G3/8, monostable, central stable position





CC = Centres Closed CO = Centres Open



_33.6








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
463-33	in-line/on manifold	5/3 CC	1600	2.5	-0.9 ÷ 10	VP08
473-33	in-line/on manifold	5/3 CO	1600	2.5	-0.9 ÷ 10	VP09

5/2-way valve, G1/2 port, monostable Mod. 452C-35








Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
452C-35	in-line	5/2	2500	2.5	-0.9 ÷ 10


C₹ CAMOZZI

5/2-way valve, G1/2 port, bistable Mod. 452C












Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
452C-33	in-line	5/2	2500	2	-0.9 ÷ 10	VP06
452C-34	in-line	5/2	2500	2	-0.9 ÷ 10	VP05

5/2-way valve, G1/2 port, monostable Mod. 452N-35











	4	2 VP04
	1	
14	5	1113


Mod.	Mounting	Function	Flow rate Qn (Nl/min)	Min. pilot pressure (bar)	Working pressure (bar)
452N-35	in-line	5/2	4000	2.5	-0.9 ÷ 10

5/2-way valve, G1/2 port, bistable Mod. 452N-33











Mod.	Mounting	Function	Flow rate Qn (Nl/min)	min. pilot Pressure (bar)	Working pressure (bar)	Symbol
452N-33	in-line	5/2	4000	2	-0.9 ÷ 10	VP06

Manifold base with common exhausts



For valves Series 4, G1/8 (3/2, 5/2 or 5/3-way)


The following is supplied with:

1x manifold

1x pair of fixing screws for valve position

1x interface seal for valve positions

2x guides for valve position



Н

DIMENSIONS												
Mod.	Α	В	С	D	E	F	G	Н	L1	L2	М	N
CNVL-42	28	33	69.2	46	12	29	23.5	78	89	77	4.3	14
CNVL-43	28	33	69.2	46	12	29	23.5	78	122	110	4.3	14
CNVL-44	28	33	69.2	46	12	29	23.5	78	155	143	4.3	14
CNVL-45	28	33	69.2	46	12	29	23.5	78	188	176	4.3	14
CNVL-46	28	33	69.2	46	12	29	23.5	78	221	209	4.3	14

Manifold base with common exhausts




For valves Series 4, G1/4 (3/2, 5/2 or 5/3-way) The following is supplied :


1x manifold

1x pair of fixing screws for valve position

1x interface seal for valve positions

2x guides for valve position





DIMENSIONS												
Mod.	Α	В	С	D	Е	F	G	Н	L1	L2	М	N
CNVL-52	30	34	84.5	53	26	40	35	95	94	82	4.3	15
CNVL-53	30	34	84.5	53	26	40	35	95	128	116	4.3	15
CNVL-54	30	34	84.5	53	26	40	35	95	162	150	4.3	15
CNVL-55	30	34	84.5	53	26	40	35	95	196	184	4.3	15
CNVL-56	30	34	84.5	53	26	40	35	95	230	218	4.3	15

Manifold base with common exhausts



For valves Series 4, G3/8 (3/2, 5/2 or 5/3-way)


The following is supplied with:

1x manifold


1x pair of fixing screws for valve position

1x interface seal for valve positions

2x guides for valve position



G3/4



Mod.	Α	В	C	D	E	F	G	Н	L1	L2	M
CNVL-62	29.5	35	108	70	19.5	39	33.5	120	94.5	82.5	5.5
CNVL-63	29.5	35	108	70	19.5	39	33.5	120	130	118	5.5
CNVL-64	29.5	35	108	70	19.5	39	33.5	120	166	154	5.5
CNVL-65	29.5	35	108	70	19.5	39	33.5	120	201	189	5.5
CNVL-66	29.5	35	108	70	19.5	39	33.5	120	237	225	5.5



Blanking plug Mod. TCNVL for manifolds



The following is supplied: 1x blanking plug 1x 0-Ring

TCNVL/3: for Series 4, G1/8 TCNVL/5: for Series 4, G1/4 TCNVL/6: for Series 4, G3/8



Mod.
TCNVL/3
TCNVL/5
TCNVL/6


Blanking plate Mod. CNVL for manifolds



The following is supplied: 2x fixing screws 3x O-Rings

CNVL/2: for Series 4, G1/8 CNVL/3: for Series 4, G1/4 CNVL/6: for Series 4, G3/8





DIMENSIONS											
Mod.	Α	В	Н	I	М	Р	Q	R			
CNVL/2	5	25.6	52	32	4.2	17	17	18			
CNVL/3	5	27.8	70	33.5	4.2	18	3.5	48.5			
CNVL/6	5	27.8	85	33.5	4.2	24.5	24.5	36			

It is used to blank vacant positions of a manifold.