

Series PG digital pressure gauges

Possibility of a direct mounting with rear or panel connection





- » Pressure unit on display
- » Battery-powered / with cable
- » Easy and fast read out with digital display
- » 4 user programmable pressure units available
- » Power saving mode
- » Back light
- » Dust-proof and splash-proof (IP65 protection class)

The new Series PG digital pressure gauges meet the need of an even more precise pressure adjustment, above all in proportional control. Thanks to the IP65 protection class these

pressure gauges are particularly suitable for applications where the highest environmental protection is required. SERIES PG DIGITAL PRESSURE GAUGES

TECHNICAL DATA

CHARACTERISTICS

S	
ij	
9	
A	
G	
R	
5	
SSI	
ũ.	
R	
N.	
E	
$\underline{\circ}$	
\Box	
Ð	
P	
Ш	
R	
S	
51	


	Vacuum	Pressure			
	PGVB	PGPB			
Pressure units	psi, bar, mmHg, kPa	psi, bar, kgf/cm², MPa			
	programmable by the user	programmable by the user			
Rated pressure range	0 ÷ -1 bar	0 ÷ 10 bar			
Display pressure range	0.1 ÷ -1 bar	-0.1 ÷ 10 bar			
Withstand pressure	3 bar	15 bar			
Repeatability	≤ ± 1% F.S. ± 1 digit	≤ ± 0,2% F.S. ± 1 digit			
Resolution: kPa	1	-			
MPa	-	0.001			
kgf/cm ²	0.01	0.01			
bar	0.01	0.01			
psi	0.1	0.1			
Indicator accuracy	≤ ± 2% F.S. ± 1 digit (ambi	ent temperature: 25 ± 3°C)			
Medium	Filtered air, incombustibl	e and non-corrosive gases			
Back light	Y	es			
Sample rate	2 Hz (2 tim	es/second)			
LCD display	3 ½ digit,	3 ½ digit, 7 segment			
Environment: Protection class	IP65 (an air tube must be installed to maintain this grade)				
Temperature	Operation: 0 ÷ 50°C				
leniperatare	Storage: -10 ÷ 60°C				
		on or freezing)			
Relative humidity	Operation/storage: 35 ÷ 85% RH				
	(no cond	(no condensation)			
Vibrations	Total amplitude 1.5mm or 10G				
	10Hz-55Hz-10Hz scan for 1 minute				
		rection of X, Y and Z			
Shock	100 m/	s² (10G)			
SHUCK		rection of X, Y and Z			
Changes due to temperature		vithin the operating temperature range			
Pneumatic connections ports		or G1/8 - M5			
FOR BATTERY-POWERED PRESSURE GAUGES ONLY					
Battery: Type	CR 2032	lithium			
Life		imes/day)			
Low-power indicator	Y	25			
Replacement	Y	es			
Turn-on interval	Display turns off	after 60 seconds			
FOR PRESSURE GAUGES WITH POWER SUPPLY CABLE ONLY					
Supply voltage	from 12 to 28 V	DC±10% Ripple			
Power consumption		mA			
Maximum voltage	1000V AC in 1-min (between the casing and the cables)				
Isolation resistance	50 Mohm min (at 500 V DC, bety	ween the casing and the cables)			
Isolation resistance Electrical connection: for pressure gauges PG2		ween the casing and the cables) e cable, length 2 m			



PG	010	-	Р	В	-	1/8	-	2
PG	SERIES							
010	BOTTOM SCALE: 010 = 10 bar 001 = -1 bar							
Р	PRESSURE RANGE: P = pressure V = vacuum							
В	LIGHTING: B = back light							
1/8	PNEUMATIC CONNECTION 1/8 = G 1/8 BSPP; M5 1/4 = G 1/4 BSPP; M5 (f		version only)					
2	ELECTRICAL CONNECTION 2 = with unshielded 2- M = with cable of 150 n	pole cable of 2 m						

Series PG digital pressure gauges - battery-powered






Mod. PG010-PB-1/8 PG001-VB-1/8 PG010-PB-1/4 PG001-VB-1/4

Series PG digital pressure gauges - with cable






Mod. PG010-PB-1/8-2 PG001-VB-1/8-2 PG010-PB-1/8-M PG001-VB-1/8-M

Mounting brackets Mod. PG-B



Supplied with: 1x bracket type A 1x bracket type B 2x screws M3x6




Mod. PG-B

Panel mounting adapter Mod. PG-F



Supplied with: 1x adapter type A 1x adapter type B



Mod. PG-F