Coalescing filters Series MX

MX2 ports: G3/8, G1/2, G3/4 - MX3 ports: G3/4, G1 Modular Bowl with technopolymer cover and bayonet-type mounting



The Series MX air treatment components are characterized by a modern, linear and compact design, offering high performances. The perfect integration between metal alloys and technopolymers has allowed the realization of a reliable product, light and strong at the same time. Thanks to a new concept of modularity, moreover, the mounting of components has become easier.



The Series MX has been realized to offer a multi-sector solution that guarantees saving in terms of installation time, space and costs.

A special configurator, available on Camozzi website at http://catalogue. camozzi.com (sec. Configurators), allows the customer to choose the most suitable solution for his application, selecting single components or by configuring assembled FRLs.

- » High performance and compressed air quality (according to ISO 8573-1)
- » Quality of delivered air according to ISO 8573-1:2010, Classes 1.8.1 and 2.8.2
- » Manual, automatic or depressing drain
- » Polymer bowl locking system
- » Visual blockage indicator

GENERAL DATA									
Construction	modular, compact								
Materials	see TABLE OF MATERIALS on the following page								
Ports	MX2: G3/8, G1/2, G3/4 - MX3: G3/4, G1								
Condensate capacity	MX2: 55 cm ³ - MX3: 85 cm ³								
Mounting	vertical in-line or wall-mounting (by means of clamps)								
Operating temperature	-5°C ÷ 50°C up to 16 bar (with the dew point of the fluid lower than 2°C at the min. working temp.) -5°C ÷ 60°C up to 10 bar (with the dew point of the fluid lower than 2°C at the min. working temp.)								
Draining of condensate	manual-semi automatic (standard), automatic, depressurization protected, direct G1/8 exhaust								
Nominal flow	see FLOW DIAGRAMS on the following pages								
Quality of delivered air according to ISO 8573-1:2010	Class 2.8.2 with 1 μm filtering element; Class 1.8.1 with 0.01 μm filtering element								
Residual oil content with inlet at 3 mg/m ³	< 0.01mg/m³ < 0.1mg/m³								
Oil retain efficiency	99.80% 97%								
Particles retain efficiency	99.99999% 99.999%								
Fluid	compressed air								
Pre-filtering with filtering element of 1µm Pre-filtering with filtering element of 0.01µm	it is recommended to use a filter of $5\mu m$ it is recommended to use a filter of $1\mu m$								


CODING EXAMPLE

МХ	2 - 1/2 - FC 0 0 1 - LH
MX	SERIES
2	SIZE: 2 = G3/8 - G1/2 - G3/4 3 = G3/4 - G1
1/2	PORTS: 3/8 = 63/8 1/2 = 61/2 3/4 = 63/4 1 = 61
FC	COALESCING FILTER
0	FILTERING ELEMENT: 0 = 0,01 μm (standard) 1 = 1 μm
0	DRAINING OF CONDENSATE (further details in the dedicated section): 0 = semiautomatic-manual drain (standard) 3 = automatic drain 5 = depressuring drain, protected 8 = without drain, with port G1/8
1	VISUAL BLOCKAGE INDICATOR: = not present 1 = present
LH	FLOW DIRECTION: = from left to right (standard) LH = from right to left

For the assembly of a single component with fixing flanges or wall-mounting, see the section "FRL Series MX Assembled"


Coalescing filters Series MX - materials


A = Filter B = Filter with visual blockage indicator



PARTS	MATERIALS
1 = Body	Aluminium
2 = Covering	Polyacetal
3 = Bowl / bowl cover	Polycarbonate/Polyamide
4 = Filtering element	Borosilicate
5 = Upper spring	Stainless steel
6 = Piston	Anodized aluminium
7 = Visual blockage indicator	Polycarbonate
8 = Indicator body	Brass
Seals	NBR

MX2 COALESCING FILTERS FLOW DIAGRAMS







* Reference diagram for models with filtering element = 0.01 μm

Δp = Pressure drop (bar) Q = Flow (Nl/min) ** Reference diagram for models with filtering element = 1 μm

Δp = Pressure drop (bar) Q = Flow (Nl/min)

MX3 COALESCING FILTERS FLOW DIAGRAMS





* Reference diagram for models with filtering element = 0.01 μ m

** Reference diagram for models with filtering element = $1 \, \mu m$


Δp = Pressure drop (bar) Q = Flow (Nl/min) Δp = Pressure drop (bar) Q = Flow (Nl/min)

Automatio





Coalescing filters Series MX - dimensions





Mod.	Α	С	G	I.	L	М	Ν	0	R	S	Т	Weight (Kg)
MX2-3/8-FC00	G3/8	70	55,3	68	G1/8	75	212	127	85	174,5	37,5	0,5
MX2-1/2-FC00	G1/2	70	55,3	68	G1/8	75	212	127	85	174,5	37,5	0,5
MX2-3/4-FC00	G3/4	70	55,3	68	G1/8	75	212	127	85	174,5	37,5	0,5
MX3-3/4-FC00	G3/4	89,5	61,5	76	G1/8	90	241	142	99	196,5	44,5	0,8
MX3-1-FC00	G1	89,5	61,5	76	G1/8	90	241	142	99	196,5	44,5	0,8






FA01 = coalescing filter without drain with port G1/8

FA02 = coalescing filter with semiautomatic manual drain


FA03 = coalescing filter with automatic or depressuring drain

Coalescing filters with visual blockage indicator Series MX - dimensions





Mod.	А	С	D	G	Т	L	М	Ν	0	Р	R	S	Т	Weight (Kg)
MX2-3/8-FC001	G3/8	70	18.5	55.3	68	G1/8	75	231	127	19.5	85	174.5	37.5	0.5
MX2-1/2-FC001	G1/2	70	18.5	55.3	68	G1/8	75	231	127	19.5	85	174.5	37.5	0.5
MX2-1/2-FC001	G3/4	70	18.5	55.3	68	G1/8	75	231	127	19.5	85	174.5	37.5	0.5
MX3-3/4-FC001	G3/4	89.5	18.5	61.5	76	G1/8	90	260	142	19.5	99	196.5	44.5	0.9
MX3-1-FC001	G1	89.5	18.5	61.5	76	G1/8	90	260	142	19.5	99	196.5	44.5	0.9



FA04 = coalescing filter without drain, with port G1/8 and visual blockage indicator FA05 = coalescing filter with semi-automatic manual drain and visual blockage indicator FA06 = coalescing filter with automatic or depressuring drain and visual blockage indicator

Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com.