

Filters Series MX

MX2 ports: G3/8, G1/2, G3/4 - MX3 ports: G3/4, G1

Modular

Bowl with technopolymer cover and bayonet-type mounting





The Series MX air treatment components are characterized by a modern, linear and compact design, offering high performances. The perfect integration between metal alloys and technopolymers has allowed the realization of a reliable product, light and strong at the same time. Thanks to a new concept of modularity, moreover, the mounting of components has become easier.

The Series MX has been realized to offer a multi-sector solution that guarantees saving in terms of installation time, space and costs.

A special configurator, available on Camozzi website at http://catalogue.camozzi.com (Configurators section), allows the customer to choose the most suitable solution for his application, selecting single components or by configuring assembled FRLs.

- » Removal of impurities and condensate
- » High flow with minimum pressure decreases
- » Quality of delivered air according to ISO 8573-1:2010, Classes 7.8.4 and 6.8.4
- » Manual, automatic or depressuring drain
- » Polymer bowl locking system reducing the risk of accidents
- » Visual blockage indicator

GENERAL DATA

Draining of condensate

Construction modular, compact with filtering element in HDPE see TABLE OF MATERIALS on the following page Materials Ports MX2: G3/8 - G1/2 - G3/4 MX3: G3/4 - G1 Condensate capacity MX2: 55 cm3 MX3: 85 cm³ vertical in-line Mounting wall-mounting (by means of clamps) Quality of delivered air Class 6.8.4 with 5 µm filtering element according to ISO 8573-1:2010 Class 7.8.4 with 25 µm filtering element see FLOW DIAGRAMS on the following pages Nominal flow compressed air

semiautomatic-manual (standard), automatic, depressuring drain protected, direct exhaust G1/8

C₹ CAMOZZI




MX	2	-	1/2	-	F	0	0	1	-	LH

MX	SERIES
2	SIZE: 2 = G3/8 - G1/2 - G3/4 3 = G3/4 - G1
1/2	PORT: 3/8 = G3/8 1/2 = G1/2 3/4 = G3/4 1 = G1
F	FILTER
0	FILTERING ELEMENT: 0 = 25 μm (standard) 1 = 5 μm
0	DRAINING OF CONDENSATE (further details in the dedicated section): 0 = semiautomatic-manual drain (standard) 3 = automatic drain 5 = depressuring drain, protected 8 = without drain, with port G1/8
1	VISUAL BLOCKAGE INDICATOR: = not present 1 = present
LH	FLOW DIRECTION: = from left to right (standard) LH = from right to left

For the assembly of a single component with fixing flanges or wall-mounting, see the section "FRL Series MX Assembled"


Filters Series MX - materials


A = Filter B = Filter with visual blockage indicator



PARTS	MATERIALS
1 = Body	Aluminium
2 = Covering	Polyacetal
3 = Bowl / bowl cover	Polycarbonate/Polyamide
4 = Valve-guide	Polyacetal
5 = Filtering element	Polyethylene
6 = Separation deflector	Polyacetal
7 = Upper spring	Stainless steel
8 = Piston	Anodized aluminium
9 = Visual blockage indicator	Polycarbonate
10 = Indicator body	Brass
Seals	NBR

MX2 FILTERS FLOW DIAGRAMS







* Reference diagram for models with filtering element = 25 μm

Δp = Pressure drop (bar) Q = Flow (Nl/min) ** Reference diagram for models with filtering element = 5 μm

Δp = Pressure drop (bar) Q = Flow (Nl/min)

MX3 FILTERS FLOW DIAGRAMS





* Reference diagram for models with filtering element = 25 μ m


Δp = Pressure drop (bar) Q = Flow (Nl/min) ** Reference diagram for models with filtering element = $5 \mu m$

Δp = Pressure drop (bar) Q = Flow (Nl/min)

C₹ CAMOZZI

Filters Series MX - dimensions





Mod.	Α	C	G	- 1	L	М	N	0	R	S	T	Weight (Kg)
MX2-3/8-F00	G3/8	70	55.3	68	G1/8	80	212	127	85	174.5	37.5	0.5
MX2-1/2-F00	G1/2	70	55.3	68	G1/8	80	212	127	85	174.5	37.5	0.5
MX2-3/4-F00	G3/4	70	55.3	68	G1/8	80	212	127	85	174.5	37.5	0.5
MX3-3/4-F00	G3/4	89.5	61.5	76	G1/8	95	241	142	99	196.5	44.5	0.8
MX3-1-F00	G1	89.5	61.5	76	G1/8	95	241	142	99	196.5	44.5	0.8








FT01 = filter with direct G1/8 exhaust FTO2 = filter with semi-automatic manual drain

FT03 = filter with automatic/ depressuring drain

Filters Series MX - dimensions





Mod.	Α	С	D	G	- 1	L	М	N	0	Р	R	S	T	Weight (Kg)
MX2-3/8-F001	G3/8	70	18.5	55,3	68	G1/8	80	231	127	19.5	85	174,5	37.5	0,5
MX2-1/2-F001	G1/2	70	18.5	55,3	68	G1/8	80	231	127	19.5	85	174,5	37.5	0,5
MX2-3/4-F001	G3/4	70	18.5	55,3	68	G1/8	80	231	127	19.5	85	174,5	37.5	0,5
MX3-3/4-F001	G3/4	89,5	18.5	61,5	76	G1/8	95	260	142	19.5	99	196,5	44,5	0,8
MX3-1-F001	G1	89,5	18.5	61,5	76	G1/8	95	260	142	19.5	99	196,5	44,5	0,8



FT05 = filter with direct G1/8 exhaust and visual blockage indicator FT06 = filter with semi-automatic manual drain and visual blockage



FT07

indicator FT07 = filter with automatic/ depressuring drain and visual blockage indicator