OX1 fittings and accessories for applications of medical gases



Tube external diameters: 4, 6 and 8 mm

Fittings threads: metric (M5), BSP (G1/8, G1/4), BSPT (R1/8, R1/4)



OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL











OX1 fittings are designed for the Life Science market, particularly for medical and analytical applications.

Equipment manufacturers of Ventilators, Anaesthesia devices, Oxygen Concentrators, Mass Spectrometry or Bio Medical analysers have qualified the Series OX1 fittings for many years.

OX1 Products Cleanliness level: Non volatile residue equal to or less than 550 mg/m2

Level OX1: ultrasonic cleaning of components, inspection with UV black light, lubrication with a specific grease suitable to be used with oxygen.

- » Ultrasonic cleaning
- » Oxygen suitable grease
- » Approved Collet technology
- » Long life service
- » Use with PA, PU, PE or Fluoropolymer Tubings

Serie 6000 OX1 push in fittings:

Series 6000 OX1 super-rapid fittings have been designed with a special collet which provides an homogeneous tight on the whole surface of plastic tubes, thus ensuring high reliability and a long service life, also after connections and disconnections of the tube are repeated several times.

Series VNR OX1 unidirectional valves:

They are available with Integrated Push-in Fittings. Thanks to their construction they operate at low pressure.

Series 2000 OX1 brass pipe fittings:

The wide range of Camozzi pipe fittings, which includes straight, L and Tee, male or female couplings, guarantees the necessary support during the design of medical and analytical systems.



GENERAL CHARACTERISTICS

Series 6000	
Diameters	ø 4, 6 and 8mm
Threads	GAS cylindrical ISO 228 (BSP); M5
Temperature	-15 °C \div 80 °C (see the technical data of tubing used)
Tube to connect	Polyamide (PA) 6 - 11 - 12, Polyurethane (PU), Fluoropolymer (FEP)
Fluid	Oxygen, Medical Gazes, Compressed Air or Other low pressure fluids
Materials	Standard models: body and collet in nickel-plated brass, O-ring with FKM with Oxygen suitable grease.
Working pressure	Standard models: min -0,9 bar - max 16 bar (see tubing)

Valve group	automatic valves
Construction	poppet-type
Materials	brass body stainless steel spring FKM seals
Mounting	in any position
Dimensions tube version	Ø4; Ø6; Ø8
Operating temperature	0 °C ÷ 80 °C
Fluid	Oxygen, Medical Gases, Compressed Air or Other low pressure fluids

Series 20	000
-----------	-----


Threads	GAS conical ISO 7 (BSPT) GAS cylindrical ISO 228 (BSP)
Temperature	-40 °C ÷ 120 °C
Fluid	Oxygen, Medical Gases, Compressed Air or Other low pressure fluids
Materials	nickel-plated brass
Working pressure	80 bar
-	



Fittings Mod. 6512-0X1








DIMENSIONS										
Mod.	Α	D	С	F	G	Н	L	SW	SW1	Weight (g)
6512 4-M5-OX1	4	M5	14.0	7.8	8.8	4	20	8	2	4
6512 4-1/8-0X1	4	G1/8	14.0	8.8	13.5	6	19	12	2.5	10
6512 6-M5-0X1	6	M5	16.0	11.7	13.2	4	22	12	2	8
6512 6-1/8-0X1	6	G1/8	16.0	11.7	13.5	6	21	12	4	10
6512 6-1/4-0X1	6	G1/4	16.0	11.7	16.4	7	22	15	4	13
6512 8-1/8-0X1	8	G1/8	17.5	13.7	15.2	6	26	14	5	15
6512 8-1/4-0X1	8	G1/4	17.5	13.7	16.4	7	24.5	15	6	17

Fittings Mod. 6700-0X1

Cartridge



S* = for both metallic and synthetic seat




Mod.	АВ	С	D	DE	F	G	Н	H2	J	K	L	P min	P max	S (+0,01/-	Weight
								(+0,1/0)				(Kg)	(Kg)	0,04)	(g)
6700 4-0X1	4 3.5	0.5x45°	8.8	14	8.6	9	11	3.3	15°	0.5	14.5	200	360	8.75	4
6700 6-0X1	6 4	0.5x45°	12	17	11.8	12.2	12	3.8	15°	0.5	16.5	160	570	11.95	8

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 6463-0X1








DIMENSIONS									
Mod.	Α	D	С	F	G	L	P (min)	SW	Weight (g)
6463 4-1/8-0X1	4	G1/8	10	9	13	24	6	12	14
6463 6-1/8-0X1	6	G1/8	10	11.7	13	26	6	12	14
6463 6-1/4-0X1	6	G1/4	11.5	11.9	16.5	27.5	7	15	23

Fittings Mod. 6522-0X1

Metric-BSP Swivel Male Elbow





DIMENSIONS										
DIMENZIONZ										
Mod.	Α	D	С	E	F	Н	М	SW	SW1	Weight (g)
6522 4-M5-0X1	4	M5	14.0	12.5	9	4	17.5	8	8	12
6522 4-1/8-0X1	4	G1/8	14.0	14.5	9	6	17.5	8	12	15
6522 6-M5-0X1	6	M5	16.0	13	12.7	4	20	9	10	14
6522 6-1/8-0X1	6	G1/8	16.0	15	12.7	6	20	9	12	19
6522 6-1/4-0X1	6	G1/4	16.0	16	12.7	7	20	9	15	27
6522 8-1/8-0X1	8	G1/8	17.5	16	14.2	6	22.5	11	12	22
6522 8-1/4-0X1	8	G1/4	17.5	17	14.2	7	22.5	11	15	28

8.01.04




Fittings Mod. 6590-0X1

New

Bulkhead Connector





DIMENSIONS										
Mod.	Α	В	F	L	N	MAX	SW	SW1	T	Weight (g)
6590 4-0X1	4	M10x1	8.8	29	14	10.5	14	14	20	16
6590 6-0X1	6	M14x1	12.5	33	16	10.5	17	17	20	28

Fittings Mod. 6580-0X1

New



Union Connector

SZ	ļ -		G
 <i>γ</i>	S1		z
		■ A F	


DIMENSIONS									
Mod.	Α	F	G	L	N	S	S1	S2	Weight (g)
6580 4-0X1	4	8.4	9	29	14	5	2.2	1.6	11
6580 6-0X1	6	11.7	12	34	16	5	2.2	1.6	16
6580 8-0X1	8	13.7	14	37	17.5	5	2.2	1.6	23

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 6550-0X1

Elbow connector






DIMENSIONS						
Mod.	Α	С	F	М	SW	Weight (g)
6550 4-0X1	4	3.5	9	17.5	8	8
6550 6-0X1	6	4	12.7	20	9	17

Fittings Mod. 6540-0X1

New

Tee Connector





DIMENSIONS							
Mod.	Α	С	F	L	М	SW	Weight (g)
6540 4-0X1	4	3.5	9	35	17.5	8	14
6540 6-0X1	6	4	12.7	40	20	9	24




Fittings Mod. 6560-0X1

New







DIMENSIONS						
Mod.	Α	С	F	L	M	Weight (g)
6560 4-0X1	4	5	18	33	9	19
6560 6-0X1	6	7	24.5	39	12.5	30

Fittings Mod. 6750-0X1

New



Female Plug




DIMENSIONS				
Mod.	А	G	L	Weight (g)
6750 4-0X1	4	8.8	15	4
6750 6-0X1	6	11.8	17	7

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 6800-0X1



Reducer Junction




DIMENSIONS							
Mod.	Α	G	С	F	L	T	Weight (g)
6800 4-6-0X1	4	6	15.5	9	29.5	18	9
6800 4-8-0X1	4	8	18	9	32	20.5	10
6800 6-8-0X1	6	8	18	12 7	34	20.5	12

Fittings Mod. 6555-0X1

New

Junction Elbow





DIMENSIONS									
Mod.	Α	G	С	L	F	T	М	SW	Weight (g)
6555 6-6-0X1	6	6	4	24.5	12.7	18	20	9	14




Accessory Mod. 6900-0X1





Plastic Male Plug





DIMENSIONS					
Mod.	G	L	Р	T	Weight (g)
6900 4-0X1	4	29	8	20	1
6900 6-0X1	6	31.5	8	22.5	1

Series VNR unidirectional valves

New










OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 2500-0X1



BSPT Nipple




DIMENSIONS					
Mod.	А	Н	L	SW	Weight (g)
2500 1/8-0X1	R1/8	7,5	19,5	12	9
2500 1/4-0X1	R1/4	11	27	14	16

Fittings Mod. 2501-0X1

New

Metric-BSP Nipple





DIMENSIONS					
Mod.	А	Н	L	SW	Weight (g)
2501 1/8-0X1	G1/8	6	16,5	13	9
2501 1/4-0X1	G1/4	8	21	17	15




Fittings Mod. 2510-0X1

New

BSPT Reducing Nipple





DIMENSIONS							
Mod.	A1	A2	H2	H1	L	SW	Weight (g)
2510 1/8-1/4-0X1	R1/8	R1/4	11	7,5	23,5	14	14

Fittings Mod. 2531-0X1

New

BSP Reducing





DIMENSIONS							
Mod.	Α	В	Н	L	SW	Weight (g)	
2531 1/8-M5-0X1	G1/8	M5	6	10,5	13	8	*
2531 1/4-1/8-0X1	G1/4	G1/8	8	13	17	11	*


* = with through-out thread

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 2543-0X1







DIMENSIONS				
Mod.	В	L	SW	Weight (g)
2543 M5-0X1	M5	11	8	3
2543 1/8-0X1	G1/8	15	13	8
2543 1/4-0X1	G1/4	22	17	19

Fittings Mod. 2611-0X1

BSP Male Plug





DIMENSIONS								
Mod.	А	Н	L	SW	Weight (g)			
2611 M5-0X1	M5	4	7,5	8	2			
2611 1/8-0X1	G1/8	6	10,5	13	7			
2611 1/4-0X1	G1/4	8	13	17	13			




Fittings Mod. 2013-0X1

New

BSPT Female Elbow






DIMENSIONS				
Mod.	В	М	SW	Weight (g)
2013 1/8-0X1	G1/8	19	11	16
2017 1/6 OV1	C1 //	77	1.6	20

Fittings Mod. 2021-0X1 and 2020-0X1

New

Mod. 2021-OX1: Metric Male Female Elbow Mod. 2020-OX1: BSPT Male Female Elbow






DIMENSIONS								
Mod.	Α	В	E	Н	M	P (min)	SW	Weight (g)
2020 1/8-1/8-0X1	R1/8	G1/8	11,5	8,5	19	6	11	17
2020 1/4-1/4-0X1	R1/4	G1/4	15	11	23	7	13	27

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL

Fittings Mod. 2003-0X1

Female Tee






DIMENSIONS				
Mod.	В	М	SW	Weight (g)
2003 1/8-0X1	G1/8	19	12	23
2003 1/4-0X1	G1/4	23	13	39

Fittings Mod. 2043-0X1

Female Y





DIMENSIONS								
Mod.	В	F	L	М	M1	Р	SW	Weight (g)
2043 1/8-0X1	G1/8	14,5	26,5	14	12	8	13	18
2043 1/4-0X1	G1/4	18	32	17.5	14	11	17	32