

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A08A135

Datasheet creation date: 07/03/2025 18:00

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                           |  |
|---------------------------|--|
| <b>Series (mm)</b>        | 16   |
| <b>Bore (mm)</b>          | 8  |
| <b>Version</b>            | N = standard   |
| <b>Operation</b>          | 2 = double acting  |
| <b>Materials</b>          | A = rolled stainless steel stem - stainless steel jacket |
| <b>Construction</b>       | A = ring nut V + stem nut U                              |
| <b>Stroke type</b>        | variable   |
| <b>Stroke (mm)</b>        | 135  |
| <b>Rod seals material</b> | = standard   |
| <b>Extended rod (mm)</b>  | 0  |

## Minicylinders - Series 16 - 23 - 24 - 25

Product code: 16N2A08A135



### DIMENSIONS

|          |          |
|----------|----------|
| EW (mm)  | 8        |
| KW (mm)  | 7        |
| BE       | M12x1,25 |
| KK       | M4x0.7   |
| ØCD (mm) | 4        |
| D1 (mm)  | 9.3      |
| EE       | M5       |
| ØD2 (mm) | 4        |
| L1 (mm)  | 221.0    |
| XC (mm)  | 199      |
| L2 (mm)  | 181.0    |
| AM (mm)  | 12       |
| L3 (mm)  | 10       |
| L4 (mm)  | 4.5      |
| L5 (mm)  | 12       |
| L (mm)   | 6        |
| WF (mm)  | 16       |
| L6 (mm)  | 9        |
| L7 (mm)  | 28       |
| KV (mm)  | 19       |
| SW (mm)  | -        |
| D (mm)   | 15.0     |
| D3 (mm)  | 15       |