

OX1 fittings and accessories for applications of medical gases

Tube external diameters: 4, 6 and 8 mm Fittings threads: metric (M5), BSP (G1/8, G1/4), BSPT (R1/8, R1/4)



OX1 fittings are designed for the Life Science market, particularly for medical and analytical applications.

Equipment manufacturers of Ventilators, Anaesthesia devices, Oxygen Concentrators, Mass Spectrometry or Bio Medical analysers have qualified the Series OX1 fittings for many years. OX1 Products Cleanliness level: Non volatile residue equal to or less than 550 mg/m2

Level OX1 : ultrasonic cleaning of components, inspection with UV black light, lubrication with a specific grease suitable to be used with oxygen.

- » Ultrasonic cleaning
- » Oxygen suitable grease
- » Approved Collet technology
- » Long life service
- » Use with PA, PU, PE or Fluoropolymer Tubings

Serie 6000 OX1 push in fittings:

Series 6000 OX1 super-rapid fittings have been designed with a special collet which provides an homogeneous tight on the whole surface of plastic tubes, thus ensuring high reliability and a long service life, also after connections and disconnections of the tube are repeated several times.

Series VNR OX1 unidirectional valves:

They are available with Integrated Push-in Fittings. Thanks to their construction they operate at low pressure.

Series 2000 OX1 brass pipe fittings:

The wide range of Camozzi pipe fittings, which includes straight, L and Tee, male or female couplings, guarantees the necessary support during the design of medical and analytical systems.



GENERAL CHARACTERISTICS

ø 4, 6 and 8mm
GAS cylindrical ISO 228 (BSP); M5
-10 °C \div 80 °C (see the technical data of tubing used)
Polyamide (PA) 6 - 11 - 12, Polyurethane (PU), Fluoropolymer (FEP)
Oxygen, Medical Gazes, Compressed Air or Other low pressure fluids
Standard models: body and collet in nickel-plated brass, O-ring with FKM with Oxygen suitable grease.
Standard models: min -0,9 bar - max 16 bar (see tubing)

Construction Materials Mounting Dimensions tube version	poppet-type brass body stainless steel spring FKM seals in any position
Mounting	stainless steel spring FKM seals
-	in any position
Dimensions tube version	in any position
	Ø4; Ø6; Ø8
Operating temperature	0 °C ÷ 80 °C
Fluid Oxygen,	n, Medical Gases, Compressed Air or Other low pressure fluids


Series 2000	
Threads	GAS conical ISO 7 (BSPT) GAS cylindrical ISO 228 (BSP)
Temperature	-40 °C + 120 °C
Fluid	Oxygen, Medical Gases, Compressed Air or Other low pressure fluids
Materials	nickel-plated brass
Working pressure	80 bar



Fittings Mod. 6512-0X1

Metric-BSP Male Connector






DIMENSIONS										
Mod.	А	D	С	F	G	Н	L	SW	SW1	Weight (g)
6512 4-M5-OX1	4	M5	14.0	7.8	8.8	4	20	8	2	4
6512 4-1/8-0X1	4	G1/8	14.0	8.8	13.5	6	19	12	2.5	10
6512 6-M5-OX1	6	M5	16.0	11.7	13.2	4	22	12	2	8
6512 6-1/8-0X1	6	G1/8	16.0	11.7	13.5	6	21	12	4	10
6512 6-1/4-0X1	6	G1/4	16.0	11.7	16.4	7	22	15	4	13
6512 8-1/8-0X1	8	G1/8	17.5	13.7	15.2	6	26	14	5	15
6512 8-1/4-0X1	8	G1/4	17.5	13.7	16.4	7	24.5	15	6	17


Fittings Mod. 6700-0X1

Cartridge



S* = for both metallic and synthetic seat





Mod.	А	В	С	D	DE	F	G	Н	H2(+0,1/0)	J	К	L	P min (Kg)	P max (Kg)	S(+0,01/-0,04)	Weight (g)
6700 4-0X1	4	3.5	0.5x45°	8.8	14	8.6	9	11	3.3	15°	0.5	14.5	200	360	8.75	4
6700 6-0X1	6	4	0.5x45°	12	17	11.8	12.2	12	3.8	15°	0.5	16.5	160	570	11.95	8


8.01.03



Fittings Mod. 6463-0X1

Metric-BSP Female Connector






DIMENSIONS									
Mod.	А	D	С	F	G	L	P (min)	SW	Weight (g)
6463 4-1/8-0X1	4	G1/8	10	9	13	24	6	12	14
6463 6-1/8-0X1	6	G1/8	10	11.7	13	26	6	12	14
6463 6-1/4-0X1	6	G1/4	11.5	11.9	16.5	27.5	7	15	23

Fittings Mod. 6522-0X1

Metric-BSP Swivel Male Elbow





DIMENSIONS										
Mod.	А	D	С	E	F	Н	М	SW	SW1	Weight (g)
6522 4-M5-0X1	4	M5	14.0	12.5	9	4	17.5	8	8	12
6522 4-1/8-0X1	4	G1/8	14.0	14.5	9	6	17.5	8	12	15
6522 6-M5-0X1	6	M5	16.0	13	12.7	4	20	9	10	14
6522 6-1/8-0X1	6	G1/8	16.0	15	12.7	6	20	9	12	19
6522 6-1/4-0X1	6	G1/4	16.0	16	12.7	7	20	9	15	27
6522 8-1/8-0X1	8	G1/8	17.5	16	14.2	6	22.5	11	12	22
6522 8-1//-OX1	8	61/4	175	17	14.2	7	22.5	11	15	28

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL GASES




New

New

Fittings Mod. 6590-0X1

Bulkhead Connector





DIMENSIONS										
Mod.	А	В	F	L	Ν	MAX	SW	SW1	Т	Weight (g)
6590 4-0X1	4	M10x1	8.8	29	14	10.5	14	14	20	16
6590 6-0X1	6	M14x1	12.5	33	16	10.5	17	17	20	28

Fittings Mod. 6580-0X1



Union Connector


	S2	-		G
-	s t t			z
L			/ F	

DIMENSIONS									
Mod.	А	F	G	L	Ν	S	S1	S2	Weight (g)
6580 4-0X1	4	8.4	9	29	14	5	2.2	1.6	11
6580 6-0X1	6	11.7	12	34	16	5	2.2	1.6	16
6580 8-0X1	8	13.7	14	37	17.5	5	2.2	1.6	23

Fittings Mod. 6550-0X1








DIMENSIONS						
Mod.	А	C	F	М	SW	Weight (g)
6550 4-0X1	4	3.5	9	17.5	8	8
6550 6-0X1	6	4	12.7	20	9	17

Fittings Mod. 6540-0X1

Tee Connector






DIMENSIONS							
Mod.	А	С	F	L	М	SW	Weight (g)
6540 4-0X1	4	3.5	9	35	17.5	8	14
6540 6-0X1	6	4	12.7	40	20	9	24

Fittings Mod. 6560-0X1



Y Union



DIMENSIONS						
Mod.	А	C	F	L	М	Weight (g)
6560 4-0X1	4	5	18	33	9	19
6560 6-0X1	6	7	24.5	39	12.5	30





Female Plug



DIMENSIONS				
Mod.	А	G	L	Weight (g)
6750 4-0X1	4	8.8	15	4
6750 6-0X1	6	11.8	17	7




OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL GASES

Fittings Mod. 6800-0X1



Reducer Junction






DIMENSIONS							
Mod.	А	G	С	F	L	Т	Weight (g)
6800 4-6-0X1	4	6	15.5	9	29.5	18	9
6800 4-8-0X1	4	8	18	9	32	20.5	10
6800 6-8-0X1	6	8	18	12.7	34	20.5	12

Fittings Mod. 6555-0X1

Junction Elbow





	DIMENSIONS									
555 6-6-0X1 6 6 4 24.5 12.7 18 20 9 14	Mod.	А	G	С	L	F	Т	М	SW	Weight (g)
	6555 6-6-0X1	6	6	4	24.5	12.7	18	20	9	14


New



Accessory Mod. 6900-0X1




Plastic Male Plug



DIMENSIONS					
Mod.	G	L	Р	T	Weight (g)
6900 4-0X1	4	29	8	20	1
6900 6-0X1	6	31.5	8	22.5	1

Series VNR unidirectional valves






\downarrow^2	VNR1
₹ I	

New

Mod.	A	G	L	N	Flow 6 bar ΔP1(Nl/min)	Min. operating pressure (bar)	Max operating pressure (bar)	Weight (g)
6580 4-VNR-OX1	4	9	40	14	85	0,2	10	13
6580 6-VNR-OX1	6	12	48	16	450	0,2	10	20
6580 8-VNR-OX1	8	14	52.5	17.5	900	0,2	10	30





BSPT Nipple

			<u>ا م</u>
Ì	±		
_	<u></u>		
1	1	↓ _ /	

DIMENSIONS					
Mod.	А	н	L	SW	Weight (g)
2500 1/8-0X1	R1/8	7,5	19,5	12	9
2500 1/4-0X1	R1/4	11	27	14	16

Products designed for industrial applications.
General terms and conditions for sale are available on www.camozzi.com.

OX1 FITTINGS AND ACCESSORIES FOR APPLICATIONS OF MEDICAL GASES


New

Metric-BSP Nipple

New

New

Fittings Mod. 2501-0X1



DIMENSIONS					
Mod.	А	Н	L	SW	Weight (g)
25011/8-0X1	G1/8	6	16,5	13	9
2501 1/4-0X1	G1/4	8	21	17	15

Fittings Mod. 2510-0X1



BSPT Reducing Nipple

SW A1

DIMENSIONS							
Mod.	A1	A2	H2	H1	L	SW	Weight (g)
25101/8-1/4-0X1	R1/8	R1/4	11	7,5	23,5	14	14

Fittings Mod. 2531-0X1

BSP Reducing



SW	B
↓ _±↓	

DIMENSIONS								
Mod.	А	В	Н	L	SW	Weight (g)		* = with through-out thread
2531 1/8-M5-0X1	G1/8	M5	6	10,5	13	8	*	
2531 1/4-1/8-0X1	G1/4	G1/8	8	13	17	11	*	-



Products designed for industrial applications. General terms and conditions for sale are available on www.camozzi.com.


8.01.09 177

New

Fittings Mod. 2543-0X1

Sleeve





DIMENSIONS				
Mod.	В	L	SW	Weight (g)
2543 M5-0X1	M5	11	8	3
2543 1/8-0X1	G1/8	15	13	8
2543 1/4-0X1	G1/4	22	17	19

Fittings Mod. 2611-0X1

BSP Male Plug






DIMENSIONS					
Mod.	А	Н	L	SW	Weight (g)
2611 M5-0X1	M5	4	7,5	8	2
2611 1/8-0X1	G1/8	6	10,5	13	7
26111/4-0X1	G1/4	8	13	17	13

New

Fittings Mod. 2013-0X1

BSPT Female Elbow






DIMENSIONS				
Mod.	В	М	SW	Weight (g)
2013 1/8-0X1	G1/8	19	11	16
2013 1/4-0X1	G1/4	23	14	28

Fittings Mod. 2021-OX1 and 2020-OX1



Mod. 2021-OX1: Metric Male Female Elbow Mod. 2020-OX1: BSPT Male Female Elbow




DIMENSIONS								
Mod.	А	В	E	н	М	P (min)	SW	Weight (g)
20201/8-1/8-0X1	R1/8	G1/8	11,5	8,5	19	6	11	17
20201/4-1/4-0X1	R1/4	G1/4	15	11	23	7	13	27

New

Fittings Mod. 2003-0X1

Female Tee






DIMENSIONS				
Mod.	В	М	SW	Weight (g)
2003 1/8-0X1	G1/8	19	12	23
2003 1/4-0X1	G1/4	23	13	39

Fittings Mod. 2043-0X1







DIMENSIONS								
Mod.	В	F	L	М	M1	Р	SW	Weight (g)
2043 1/8-0X1	G1/8	14,5	26,5	14	12	8	13	18
2043 1/4-0X1	G1/4	18	32	17,5	14	11	17	32