

PRECISION REGULATORS WITH MANUAL OVERRIDE

SERIES PR

Size 1 ports: G1/4
Size 2 ports: G1/4, G3/8



- High precision adjustment
- Multi-diaphragm construction to reach the highest stability
- Adjustment lock
- Compact dimensions
- Removable adjustment knob

The Series PR precision pressure regulators are ideal for applications that require a precise and stable air pressure control. The operating principle using multiple diaphragms allows the Series PR to react to even the smallest pressure variations that may occur during use.

General Data

Construction	Compact, multi-diaphragm type
Materials	See the following page
Ports	Size 1: G1/4 Size 2: G1/4, G3/8
Mounting	Vertical in-line, wall or panel mounting (in any position)
Working temperature	0°C ÷ 50°C
Inlet pressure	0.1 ÷ 12 bar
Outlet pressure	0.05 ÷ 2 bar 0.05 ÷ 4 bar 0.05 ÷ 7 bar 0.05 ÷ 10 bar
Overpressure exhaust	With relieving (standard)
Nominal flow	See Flow diagrams
Fluid	Filtered and not lubricated compressed air according to DIN ISO 8573-1 Classes 1-3-2
Hysteresis	20mbar
Repeatability [% FS]	±0.2% FS
Bleed air consumption	5 NL/min (ANR) with inlet pressure 10 bar


Coding example

PR	1	04	-	M	07
PR	SERIES				
1	SIZE 1 = size 1 2 = size 2				
04	PORTS 04 = G1/4 38 = G3/8 (size 2 only)				
M	TYPE OF ADJUSTMENT M = manual				
07	OPERATING PRESSURE (1 bar = 14,5 psi): 02 = 0.05 ÷ 2 bar 04 = 0.05 ÷ 4 bar 07 = 0.05 ÷ 7 bar 00 = 0.05 ÷ 10 bar				

Materials


AIR TREATMENT

9




Parts	Materials
1 = Body	Anodized aluminium
2 = Intermediate body	Aluminium
3 = Valve holder plug	Brass
4 = Bell	Polyamide
5 = Regulator knob	Polyamide
6 = Springs	Stainless steel
7 = Diaphragms	NBR
8 = Filters	Stainless steel
9 = Seals	NBR
10 = Piston	Aluminium
11 = Rod	Stainless steel
O-ring	NBR

Precision regulators - Size 1



PR02




Mod.	A	B	D	F	G	I	M	N	P	Q	R	S	T	U	Weight [kg]
PR104-M*	G1/4	G1/8	28	30	45	45	25	96	40	2	56	17,5	38,5	0-6	0,35

Precision regulators - Size 2



PR02




Mod.	A	B	C	D	E	F	G	I	M	N	P	Q	R	S	T	U	Weight [kg]
PR204-M*	G1/4	G1/8	42	28	4,2	30	50	50	25	140	40	2	101,8	35,5	66,3	0-6	0,645
PR238-M*	G3/8	G1/8	42	28	4,2	30	50	50	25	140	40	2	101,8	35,5	66,3	0-6	0,645

AIR TREATMENT

9


Flow diagrams Mod. PR104-M00

PR104-M00



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR104-M00



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR104-M07

PR104-M07



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR104-M07



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR104-M04

PR104-M04



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR104-M04



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR104-M02

PR104-M02



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR104-M02



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR204-M00

PR204-M00



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR204-M00



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR204-M07

PR204-M07



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR204-M07



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR204-M04

PR204-M04



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR204-M04



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR204-M02

PR204-M02



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR204-M02



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR238-M00

PR238-M00



Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


PR238-M00



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NL/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR238-M07

PR238-M07



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR238-M07



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR238-M04

PR238-M04



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR238-M04



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Flow diagrams Mod. PR238-M02

PR238-M02



Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


PR238-M02



EXHAUST FLOW
 Pr = Regulated pressure (bar)
 Q = Flow (NI/min)
 Pa = Inlet pressure (bar)


Mounting bracket Mod. C114-ST

For regulators and filter-regulators (G1/4 - G1/8)



Material:
zinc-plated steel

Supplied with:
1x bracket



Mod.
C114-ST


Mounting bracket Mod. 114-ST/1

For regulators and filter-regulators (G1/4 - G1/8)



Material:
zinc-plated steel

Supplied with:
1x bracket



Mod.
C114-ST/1


Mounting bracket Mod. C114-ST/2

For regulators and filter-regulators (G1/4 - G1/8)



Material:
zinc-plated steel

Supplied with:
1x bracket



Mod.
C114-ST/2