

S2000 系列 Sprint® 型管道接头

连接螺纹 G1/8, G1/4, G3/8, G1/2, R1/8, R1/4, R3/8, R1/2




S2000 系列 Sprint® 型管道接头 共有 14 种不同的类型，在这些接头的英制管锥螺纹上均增加了康茂胜专利设计的 Sprint® 型聚四氟乙烯密封圈，操作十分简便，且可多次装拆使用。


综合参数

连接螺纹	英制锥管螺纹 ISO 7 (BSPT) 英制圆柱管螺纹 ISO 228 (BSP)
工作温度	-40 ÷ 120°C
介质	压缩空气或低压流体
材料	镀镍黄铜基体，聚四氟乙烯连接螺纹密封件
最大工作压力	80 bar

Sprint® 型管道接头




S2500... 型管道接头




尺寸表						
型号	A	H	L	SW	质量 (g)	
S2500 1/8	R1/8	7.5	19.5	12	8	
S2500 1/4	R1/4	11	27	14	15	
S2500 3/8	R3/8	11.5	28	17	21	
S2500 1/2	R1/2	14	33.5	22	39	

S2530... 型管道接头




尺寸表						
型号	A	B	H	L	SW	质量 (g)
S2530 1/4-1/8	R1/4	G1/8	11	16	14	9
S2530 3/8-1/8	R3/8	G1/8	11.5	16.5	17	16
S2530 1/2-1/8	R1/2	G1/8	14	19.5	22	13
S2530 3/8-1/4	R3/8	G1/4	11.5	16.5	17	33
S2530 1/2-1/4	R1/2	G1/4	14	19.5	22	32
S2530 1/2-3/8	R1/2	G3/8	14	19.5	22	22

S2520... 型管道接头




尺寸表						
型号	A	B	H	L	SW	质量 (g)
S2520 1/8-1/8	R1/8	G1/8	7.5	17.5	13	11
S2520 1/8-1/4	R1/8	G1/4	7.5	19	17	15
S2520 1/8-3/8	R1/8	G3/8	7.5	20	20	19
S2520 1/4-1/4	R1/4	G1/4	11	22.5	17	17
S2520 1/4-3/8	R1/4	G3/8	11	23.5	20	33
S2520 1/4-1/2	R1/4	G1/2	11	27.5	24	34
S2520 3/8-3/8	R3/8	G3/8	11.5	24	20	36
S2520 3/8-1/2	R3/8	G1/2	11.5	28	24	56
S2520 1/2-1/2	R1/2	G1/2	14	30.5	24	41

S2510... 型管道接头




尺寸表							
型号	A1	A2	H1	H2	L	SW	质量 (g)
S2510 1/8-1/4	R1/8	R1/4	7.5	11	23.5	14	14
S2510 1/8-3/8	R1/8	R3/8	7.5	11.5	24	17	22
S2510 1/4-3/8	R1/4	R3/8	11	11.5	27.5	17	19
S2510 1/4-1/2	R1/4	R1/2	11	14	30.5	22	33
S2510 3/8-1/2	R3/8	R1/2	11.5	14	31	22	36

S2541... 型管道接头




尺寸表							
型号	A	B	H	L	SW	SW1	质量 (g)
S2541 1/8-1/8	G1/8	G1/8	5.5	28	13	14	17
S2541 1/4-1/4	G1/4	G1/4	7	31.5	17	14	26
S2541 3/8-3/8	G3/8	G3/8	8	34	20	19	39

S2010... 型管道接头




尺寸表					
型号	A	E	H	SW	质量 (g)
S2010 1/8	R1/8	11.5	7.5	9	9
S2010 1/4	R1/4	13.5	11	12	17
S2010 3/8	R3/8	15.5	11.5	14	25
S2010 1/2	R1/2	16	14	16	47

S2020... 型管道接头




尺寸表							
型号	A	B	E	H	M	SW	质量 (g)
S2020 1/8-1/8	R1/8	G1/8	11.5	8.5	19	11	16
S2020 1/4-1/4	R1/4	G1/4	15	11	23	13	27
S2020 3/8-3/8	R3/8	G3/8	15	11.5	25	15	33
S2020 1/2-1/2	R1/2	G1/2	17.5	14	31.5	20	62

S2050... 型管道接头




尺寸表								
型号	A	B	E	H	L	M	SW	质量 (g)
S2050 1/8-1/8	R1/8	G1/8	11.5	8.5	37	19	12	14
S2050 1/4-1/4	R1/4	G1/4	15	11	46	23	13	44
S2050 3/8-3/8	R3/8	G3/8	15	11.5	48.5	25	16	59
S2050 1/2-1/2	R1/2	G1/2	17.5	14	60.5	31.5	20	81

S2060... 型管道接头




尺寸表								
型号	A	B	E	H	M	SW	质量 (g)	
S2060 1/8-1/8	R1/8	G1/8	11.5	8.5	19	12	31	
S2060 1/4-1/4	R1/4	G1/4	15	11	23	13	38	
S2060 3/8-3/8	R3/8	G3/8	15	11.5	25	16	51	
S2060 1/2-1/2	R1/2	G1/2	17.5	14	31.5	20	88	

S2070... 型管道接头




尺寸表								
型号	A	B	E	H	L	M	SW	质量 (g)
S2070 1/8-1/8	R1/8	G1/8	11.5	8.5	37	19	12	30
S2070 1/4-1/4	R1/4	G1/4	15	11	46	23	13	36
S2070 3/8-3/8	R3/8	G3/8	15	11.5	48.5	25	16	51
S2070 1/2-1/2	R1/2	G1/2	17.5	14	60.5	31.5	20	89

S2080... 型管道接头




尺寸表					
型号	A	E	H	SW	质量 (g)
S2080 1/8	R1/8	11.5	7.5	9	14
S2080 1/4	R1/4	13.5	11	12	31
S2080 3/8	R3/8	15.5	11.5	14	50
S2080 1/2	R1/2	16	14	16	63

S2090... 型管道接头




尺寸表							
型号	A	B	E	H	M	SW	质量 (g)
S2090 1/8-1/8	R1/8	G1/8	11.5	8.5	19	12	22
S2090 1/4-1/4	R1/4	G1/4	15	11	23	13	16
S2090 3/8-3/8	R3/8	G3/8	15	11.5	25	16	59
S2090 1/2-1/2	R1/2	G1/2	17.5	14	31.5	20	80

2612... 型管道接头




尺寸表				
型号	A	L	SW	质量 (g)
2612 M5	M5	5.5	2	1
2612 M7	M7	7	4	2
2612 1/8	G1/8	8.5	4	5
2612 1/4	G1/4	9.5	6	9
2612 3/8	G3/8	10.5	8	17
2612 1/2	G1/2	11.5	12	25

S2610... 型管道接头



尺寸表				
型号	A	L	SW	质量 (g)
S2610 1/8	G1/8	7.5	4	3
S2610 1/4	G1/4	9	6	6
S2610 3/8	G3/8	10	8	12
S2610 1/2	G1/2	11	10	21

S2615... 型管道接头



尺寸表				
型号	A	L	SW	质量 (g)
S2615 1/8	R1/8	8	5	2
S2615 1/4	R1/4	10	7	6
S2615 3/8	R3/8	10	8	12

S2000 系列 SPRINT® 型管道接头