

## Compact magnetic cylinders - Series 32

Product code: 32F2A025A025W

Datasheet creation date: 07/03/2025 23:34

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                             |   |
|-----------------------------|---|
| <b>Series</b>               | 32  |
| <b>Ø cyl. (mm)</b>          | 25  |
| <b>Version</b>              | F=female rod thread                                 |
| <b>Operation</b>            | 2=double-acting                                     |
| <b>Materials</b>            | A = anodized aluminium body, end blocks and piston, |
| <b>Construction</b>         | A = standard  |
| <b>Stroke type</b>          | A = standard  |
| <b>Stroke Cylinder (mm)</b> | 25  |
| <b>Rod seals material</b>   | W = high temperature seals (+ 140° C) non-magnetic  |
| <b>Rod length (mm)</b>      | 0   |

## Compact magnetic cylinders - Series 32

Product code: 32F2A025A025W



### DIMENSIONS

|                 |      |
|-----------------|------|
| <b>A (mm)</b>   | 16   |
| <b>AF (mm)</b>  | 11   |
| <b>BG (mm)</b>  | 20.0 |
| <b>G (mm)</b>   | 11.9 |
| <b>Ø (mm)</b>   | 10   |
| <b>Ø (mm)</b>   | 9    |
| <b>D2 (mm)</b>  | 0    |
| <b>D3 (mm)</b>  | 0    |
| <b>D4 (mm)</b>  | 9    |
| <b>D5 (mm)</b>  | 6    |
| <b>D6 (mm)</b>  | 14   |
| <b>D7</b>       | M5   |
| <b>D8 (mm)</b>  | 5    |
| <b>E (mm)</b>   | 40.7 |
| <b>EE</b>       | M5   |
| <b>H (mm)</b>   | 8    |
| <b>KF</b>       | M6   |
| <b>KK</b>       | M8   |
| <b>LA (mm)</b>  | 5    |
| <b>L4 (mm)</b>  | 22   |
| <b>PL (mm)</b>  | 7.0  |
| <b>RT</b>       | M5   |
| <b>SW1 (mm)</b> | 8    |

|                |      |
|----------------|------|
| <b>T1 (mm)</b> | 0    |
| <b>T2 (mm)</b> | 2    |
| <b>T3 (mm)</b> | 6.5  |
| <b>TG (mm)</b> | 26.0 |
| <b>ZA (mm)</b> | 38.8 |
| <b>ZB (mm)</b> | 44.5 |
| <b>ZC (mm)</b> | 50.2 |