

## Compact magnetic cylinders - Series 32

Product code: 32M2A100A100V

Datasheet creation date: 08/03/2025 10:17

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>Series</b>	32
<b>Ø cyl. (mm)</b>	100
<b>Version</b>	M=male rod thread
<b>Operation</b>	2=double-acting
<b>Materials</b>	A = anodized aluminium body, end blocks and piston,
<b>Construction</b>	A = standard
<b>Stroke type</b>	A = standard
<b>Stroke Cylinder (mm)</b>	100
<b>Rod seals material</b>	V = rod seal in FKM
<b>Rod length (mm)</b>	0

## Compact magnetic cylinders - Series 32

Product code: 32M2A100A100V



### DIMENSIONS

<b>A (mm)</b>	28
<b>AF (mm)</b>	20
<b>BG (mm)</b>	0.0
<b>G (mm)</b>	18
<b>Ø (mm)</b>	25
<b>Ø (mm)</b>	0
<b>D2 (mm)</b>	55
<b>D3 (mm)</b>	49
<b>D4 (mm)</b>	12
<b>D5 (mm)</b>	12
<b>D6 (mm)</b>	24
<b>D7</b>	M10
<b>D8 (mm)</b>	10
<b>E (mm)</b>	115.6
<b>EE</b>	G1/8
<b>H (mm)</b>	14
<b>KF</b>	M12
<b>KK</b>	M16x1,5
<b>LA (mm)</b>	0
<b>L4 (mm)</b>	80
<b>PL (mm)</b>	8.0
<b>RT</b>	M10
<b>SW1 (mm)</b>	22

<b>T1 (mm)</b>	2
<b>T2 (mm)</b>	4
<b>T3 (mm)</b>	10.5
<b>TG (mm)</b>	89.0
<b>ZA (mm)</b>	67.0
<b>ZB (mm)</b>	76.7
<b>ZC (mm)</b>	86.4