

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 41K

Product code: 41K2P160A0125EX

Datasheet creation date: 20/05/2026 06:45

Check the most updated document online [click here](#)



### TECHNICAL DATA

|  |  |
|--|--|
| <b>SERIE (Series / mm)</b>             | 41   |
| <b>VER (Version)</b>                   | K = standard, magnetic   |
| <b>FUNZ (Operation)</b>                | 2 = double-acting (front and rear cushioning)                                    |
| <b>MAT (Materials)</b>                 | P = rolled stainless steel rod AISI 420B anodized aluminium round tube NBR seals |
| <b>PHY (Diameter / mm)</b>             | 160  |
| <b>TYP (Construction)</b>              | A = standard   |
| <b>HUB (Stroke / mm)</b>               | 125  |
| <b>OPZIONI (Seal options)</b>          | = standard   |
| <b>LSTELO (Rod length / mm)</b>        | 0  |
| <b>LSTELO2 (Rod length 2 / mm)</b>     | 0  |
| <b>OPZIONI2 (Protection options)</b>   | = standard   |
| <b>CERTIFICAZIONI (Certifications)</b> | EX = ATEX  |

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 41K

Product code: 41K2P160A0125EX



### DIMENSIONS

|                        |       |
|------------------------|-------|
| Ø MM (mm)              | 40    |
| KK                     | M36x2 |
| Ø D11 (mm)             | 65    |
| PL (mm)                | 25.5  |
| G (mm)                 | 15    |
| L1 (mm)                | 55    |
| AM (mm)                | 72    |
| VA (mm)                | 6     |
| EE                     | G3/4  |
| WH (mm)                | 80    |
| L2 (mm)                | 180   |
| ZJ                     | 260   |
| VD (mm)                | 10    |
| N (mm)                 | 50    |
| RT                     | M16   |
| BG (mm)                | 24    |
| TG (mm)                | 140   |
| E (mm)                 | 180   |
| SW1 (mm)               | 36    |
| SW3 (mm)               | 4     |
| SW4 (mm)               | 55    |
| Cushioning stroke (mm) | 33    |
| XV1±2 (mm)             | 145   |

|            |     |
|------------|-----|
| XV2±2 (mm) | 170 |
| XV3±2 (mm) | 195 |
| h14 (mm)   | 200 |
| TK (mm)    | 40  |
| e9 (mm)    | 32  |
| h14 (mm)   | 32  |
| UW (mm)    | 200 |