

## Compact cylinders - Series 31

Product code: 31F2A040A135

Datasheet creation date: 07/03/2025 19:56

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                           |                                                                |
|---------------------------|----------------------------------------------------------------|
| <b>Series</b>             | 31                                                             |
| <b>Version</b>            | F=female rod thread                                            |
| <b>Operation</b>          | 2=double-acting                                                |
| <b>Diameter (mm)</b>      | 40                                                             |
| <b>Stroke type</b>        | variable                                                       |
| <b>Stroke (mm)</b>        | 135                                                            |
| <b>Rod seals material</b> | -                                                              |
| <b>Materials</b>          | A = rolled stainless steel AISI 303 rod tube profile aluminium |
| <b>Construction</b>       | A = standard                                                   |

## Compact cylinders - Series 31

Product code: 31F2A040A135



### DIMENSIONS

|           |          |
|-----------|----------|
| Ø D (mm)  | 12       |
| Ø D1 (mm) | 5.5      |
| D2        | M6       |
| D3        | M6       |
| Ø D4 (mm) | 5        |
| D5        | M5       |
| Ø D8 (mm) | 6        |
| D9 (mm)   | 6        |
| D10 (mm)  | 17       |
| E1        | G1\8     |
| F (mm)    | 8.0      |
| F1 (mm)   | 37.5     |
| H (mm)    | 45.5     |
| H1 (mm)   | 52.0     |
| H2 (mm)   | 21.5     |
| K1        | M10x1,25 |
| L (mm)    | 60       |
| L1 (mm)   | 42       |
| L2 (mm)   | 62.5     |
| L3 (mm)   | 20       |
| L4 (mm)   | 23.3     |
| T (mm)    | 12       |
| T1 (mm)   | 22       |

|          |    |
|----------|----|
| T2 (mm)  | 4  |
| SW1 (mm) | 10 |