

## Compact magnetic cylinders - Series 32

Product code: 32M2A050A015

Datasheet creation date: 19/05/2026 08:57

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                             |   |
|-----------------------------|---|
| <b>Series</b>               | 32  |
| <b>Version</b>              | M=male rod thread                                   |
| <b>Operation</b>            | 2=double-acting                                     |
| <b>Materials</b>            | A = anodized aluminium body, end blocks and piston, |
| <b>Diameter (mm)</b>        | 50  |
| <b>Construction</b>         | A = standard  |
| <b>Cylinder Stroke (mm)</b> | 15  |
| <b>Seal options</b>         | = standard  |
| <b>Rod length (mm)</b>      | 0   |
| <b>Rod length 2 (mm)</b>    | 0   |
| <b>Certifications</b>       | = standard  |

## Compact magnetic cylinders - Series 32

Product code: 32M2A050A015



### DIMENSIONS

|                 |          |
|-----------------|----------|
| <b>A (mm)</b>   | 22       |
| <b>AF (mm)</b>  | 16       |
| <b>BG (mm)</b>  | 0.0      |
| <b>G (mm)</b>   | 14.3     |
| <b>Ø (mm)</b>   | 16       |
| <b>Ø (mm)</b>   | 0        |
| <b>D4 (mm)</b>  | 12       |
| <b>D5 (mm)</b>  | 10       |
| <b>D6 (mm)</b>  | 22       |
| <b>D7</b>       | M6       |
| <b>D8 (mm)</b>  | 6        |
| <b>E (mm)</b>   | 69.6     |
| <b>EE</b>       | G1/8     |
| <b>H (mm)</b>   | 12       |
| <b>KF</b>       | M10      |
| <b>KK</b>       | M12x1,25 |
| <b>LA (mm)</b>  | 0        |
| <b>L4 (mm)</b>  | 42       |
| <b>PL (mm)</b>  | 7.6      |
| <b>RT</b>       | M8       |
| <b>SW1 (mm)</b> | 13       |
| <b>T2 (mm)</b>  | 4        |
| <b>T3 (mm)</b>  | 7        |

|                |      |
|----------------|------|
| <b>TG (mm)</b> | 46.5 |
| <b>ZA (mm)</b> | 45.0 |
| <b>ZB (mm)</b> | 53.0 |
| <b>ZC (mm)</b> | 61   |