

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 41K

Product code: 41K2P160A0060

Datasheet creation date: 20/05/2026 06:21

Check the most updated document online [click here](#)



### TECHNICAL DATA

<b>SERIE (Series / mm)</b>	41
<b>VER (Version)</b>	K = standard, magnetic
<b>FUNZ (Operation)</b>	2 = double-acting (front and rear cushioning)
<b>MAT (Materials)</b>	P = rolled stainless steel rod AISI 420B anodized aluminium round tube NBR seals
<b>PHY (Diameter / mm)</b>	160
<b>TYP (Construction)</b>	A = standard
<b>HUB (Stroke / mm)</b>	60
<b>OPZIONI (Seal options)</b>	= standard
<b>LSTELO (Rod length / mm)</b>	0
<b>LSTELO2 (Rod length 2 / mm)</b>	0
<b>OPZIONI2 (Protection options)</b>	= standard
<b>CERTIFICAZIONI (Certifications)</b>	= standard

## Cylinders ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 41K

Product code: 41K2P160A0060



### DIMENSIONS

Ø MM (mm)	40
KK	M36x2
Ø D11 (mm)	65
PL (mm)	25.5
G (mm)	15
L1 (mm)	55
AM (mm)	72
VA (mm)	6
EE	G3/4
WH (mm)	80
L2 (mm)	180
ZJ	260
VD (mm)	10
N (mm)	50
RT	M16
BG (mm)	24
TG (mm)	140
E (mm)	180
SW1 (mm)	36
SW3 (mm)	4
SW4 (mm)	55
Cushioning stroke (mm)	33
XV1±2 (mm)	145

XV2±2 (mm)	170
XV3±2 (mm)	195
h14 (mm)	200
TK (mm)	40
e9 (mm)	32
h14 (mm)	32
UW (mm)	200