

## Cylinders - aluminium profile ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 61

Product code: 61M2P125A0500

Datasheet creation date: 08/03/2025 14:38

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                                      |   |
|--------------------------------------|---|
| <b>SERIE (Series / mm)</b>           | 61  |
| <b>PHY (Diameter / mm)</b>           | 125   |
| <b>VERSION (Version)</b>             | M = magnetic standard   |
| <b>FUNZ (Operation)</b>              | 2=double acting (front and rear cushions)   |
| <b>MAT (Materials)</b>               | P = standard: AL end-blocks and piston, rolled stainless steel AISI 420B rod, anodized AL profile tube, zinc-plated steel tie-rods and tie-rod nuts, PU seals |
| <b>TYP (Construction)</b>            | A = standard with lock nut for rod  |
| <b>HUBT (Stroke type)</b>            | variable  |
| <b>HUB (Stroke / mm)</b>             | 500   |
| <b>ES (execution)</b>                | -   |
| <b>LSTELO (extended piston / mm)</b> | 0   |

## Cylinders - aluminium profile ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 61

Product code: 61M2P125A0500



### DIMENSIONS

|                |       |
|----------------|-------|
| MM (MM / mm)   | 32    |
| KK (KK)        | M27x2 |
| B (B d11 / mm) | 60    |
| PL (PL / mm)   | 23    |
| L1 (L1 / mm)   | 42    |
| AM (AM / mm)   | 54    |
| VA (VA / mm)   | 6     |
| EE (EE)        | G1/2  |
| WH (WH / mm)   | 65    |
| L2 (L2 / mm)   | 160.0 |
| ZM (ZM / mm)   | -     |
| ZJ (ZJ / mm)   | 225   |
| VD (VD / mm)   | 8     |
| N (N / mm)     | 43.0  |
| BG (BG / mm)   | 23.0  |
| RT (RT)        | M12   |
| G (G / mm)     | 10.5  |
| TG (TG / mm)   | 110.0 |
| R (R / mm)     | 50.0  |
| E (E / mm)     | 135.0 |
| SW1 (SW1 / mm) | 27    |
| SW2 (SW2 / mm) | 12    |
| SW3 (SW3 / mm) | 4     |

|                                    |          |
|------------------------------------|----------|
| SW4 (SW4 / mm)                     | 41       |
| HUBA (Cushion stroke front spring) | 26       |
| HUBP (Cushion stroke rear spring)  | 25       |
| L3 (L3 / mm)                       | 329.0    |
| L4 (L4 / mm)                       | 22       |
| L5 (L5 / mm)                       | 30       |
| L6 (L6 / mm)                       | 51.0     |
| L7 (L7 / mm)                       | 86.5     |
| L8 (L8 / mm)                       | 140      |
| L9 (L9 / mm)                       | 160.0    |
| L10 ( / mm)                        | 350.0    |
| D (ø D / mm)                       | 32       |
| D1 (ø D1 d11 / mm)                 | 60.0     |
| D2 (ø D2 / mm)                     | 130      |
| D3 (ø D3 f6 / mm)                  | 65       |
| A (± 0.15 / mm)                    | 110.0    |
| GX (GX)                            | G1/8     |
| H (H / mm)                         | 80.0     |
| H1 (H1 / mm)                       | 150.0    |
| M (M)                              | M12      |
| Z (Z)                              | M12 x 40 |