

## End Lock cylinders - Series 63

Product code: 63MP2C063A0105FLEX

Datasheet creation date: 09/03/2025 12:34

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                                |                                       |
|--------------------------------|---------------------------------------|
| <b>Series</b>                  | 63                                    |
| <b>Version</b>                 | M = standard, magnetic                |
| <b>Construction</b>            | P= profile tube                       |
| <b>Operation</b>               | 2 = double effect                     |
| <b>Cushioning</b>              | C = cushioning on both sides          |
| <b>Bore (mm)</b>               | 63                                    |
| <b>Construction type</b>       | A = standard with rod nut             |
| <b>Stroke type</b>             | variable                              |
| <b>Stroke (mm)</b>             | 105                                   |
| <b>Stroke2 (mm)</b>            | 0                                     |
| <b>Rod length (mm)</b>         | 0                                     |
| <b>Rod length 2 (mm)</b>       | 0                                     |
| <b>Lock type</b>               | FL = Front lock                       |
| <b>Temperature range</b>       | = standard (-20°/+80°C)               |
| <b>Resistance to corrosion</b> | = Standard                            |
| <b>Manual unlock type</b>      | = manual with M3 screw (not included) |
| <b>Variants</b>                | = standard (male rod)                 |
| <b>Certifications</b>          | EX = ATEX                             |

## End Lock cylinders - Series 63

Product code: 63MP2C063A0105FLEX



### DIMENSIONS

|         |         |
|---------|---------|
| MM (mm) | 20      |
| KK      | M16x1,5 |
| B (mm)  | 45      |
| PL (mm) | 24.0    |
| PM (mm) | 27      |
| L1 (mm) | 26      |
| AM (mm) | 32      |
| VA (mm) | 4       |
| EE      | G3/8    |
| WH (mm) | 37      |
| L2 (mm) | 121     |
| L3 (mm) | 6.0     |
| L4 (mm) | 12.5    |
| ZJ (mm) | 158     |
| VD (mm) | 6       |
| N (mm)  | 37.5    |
| BG (mm) | 16.0    |
| M (mm)  | 44      |
| BF (mm) | 22.5    |
| RT (mm) | M8      |
| G (mm)  | 8.0     |
| TG (mm) | 56.5    |
| R (mm)  | 28      |

|                       |      |
|-----------------------|------|
| E (mm)                | 75   |
| F (mm)                | 77.5 |
| F1 (mm)               | 82.5 |
| SW1 (mm)              | 17   |
| SW2 (mm)              | 8    |
| SW3 (mm)              | 3    |
| SW4 (mm)              | 24   |
| Front cushioning (mm) | 19   |
| Rear cushioning (mm)  | 19.5 |