

## Rotary cylinders - Series 69

Product code: 69-040/180-M

Datasheet creation date: 07/03/2025 17:48

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                |               |
|----------------|---------------|
| Series         | 69            |
| Diameter (mm)  | 40            |
| Rotation (°)   | 180           |
| Pinion         | M=male pinion |
| Seals material | = NBR         |

## Rotary cylinders - Series 69

Product code: 69-040/180-M



### DIMENSIONS

|                   |       |
|-------------------|-------|
| <b>A (mm)</b>     | 351.5 |
| <b>B d11 (mm)</b> | 35    |
| <b>C (mm)</b>     | 40    |
| <b>D (mm)</b>     | 60    |
| <b>E (mm)</b>     | 55.0  |
| <b>F (mm)</b>     | 5     |
| <b>G (mm)</b>     | 14    |
| <b>H (mm)</b>     | 22    |
| <b>J (mm)</b>     | 25    |
| <b>K (mm)</b>     | 25    |
| <b>L (mm)</b>     | 31    |
| <b>M (mm)</b>     | 60    |
| <b>N</b>          | G1/4  |
| <b>P (mm)</b>     | 38.0  |
| <b>Q (mm)</b>     | 82.0  |
| <b>R (mm)</b>     | 30.0  |
| <b>S (mm)</b>     | 54.5  |
| <b>T</b>          | M6    |
| <b>U (mm)</b>     | 10    |
| <b>V (mm)</b>     | 16.3  |
| <b>W (mm)</b>     | 14    |
| <b>Y</b>          | M5    |
| <b>X (mm)</b>     | 12.5  |
| <b>Z (mm)</b>     | 319.5 |