

Pneumatically and electropneumatically operated valves - Series 8

Product code: 820C3105-G731Y-N004AC020

Datasheet creation date: 10/03/2025 12:02

Check the most updated document online [click here](#)




TECHNICAL DATA

| | |
|------------------------------------|-----------------------------------------------------------|
| Series | 8 |
| Size | 20 = Size 2 |
| Body design | C3 = valve with aluminium body threaded connections |
| Number of ways - Function | 1 = 2/2 NC |
| Pneumatic connections | 05= G1/4 |
| Orifice diameter | G7= 6.6mm (T2) |
| Seal material | 3 = FKM |
| Body material | 1= aluminium |
| Manual override | Y = provided monostable |
| Mounting accessories | N = not provided |
| Options | 00 = no option |
| Electrical connection | 4A = industrial standard (9.4 mm) - only for size 2 and 3 |
| Voltage - power consumption | C020= 12V DC 2 W |
| Version | = Standard |

Pneumatically and electropneumatically operated valves - Series 8

Product code: 820C3105-G731Y-N004AC020



DIMENSIONS

| | |
|------------------------------------|-----------------------------------------------------------|
| Series | 8 |
| Size | 20 = Size 2 |
| Body design | C3 = valve with aluminium body threaded connections |
| Number of ways - Function | 1 = 2/2 NC |
| Pneumatic connections | 05= G1/4 |
| Orifice diameter | G7= 6.6mm (T2) |
| Seal material | 3 = FKM |
| Body material | 1= aluminium |
| Manual override | Y = provided monostable |
| Mounting accessories | N = not provided |
| Options | 00 = no option |
| Electrical connection | 4A = industrial standard (9.4 mm) - only for size 2 and 3 |
| Voltage - power consumption | C020= 12V DC 2 W |
| Version | = Standard |