

Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M1A050A0075

Datasheet creation date: 07/03/2025 17:17

Check the most updated document online [click here](#)



TECHNICAL DATA

| | |
|------------------------|--|
| Series | 90 |
| Diameter (mm) | 50 |
| Version | M = standard magnetic |
| Operation | 1=single-acting (front spring) |
| Materials | A = stainless steel AISI 316 (SS 2343), joints NBR |
| Construction | A = standard |
| Stroke type | standard |
| Stroke (mm) | 75 |
| rod seals viton | - |

Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M1A050A0075



DIMENSIONS

| | |
|---------|---------|
| A (mm) | 32 |
| B (mm) | 40 |
| BG (mm) | 16 |
| BF (mm) | 12 |
| E (mm) | 65 |
| EE | G1/4 |
| G (mm) | 31.5 |
| KK | M16x1,5 |
| L (mm) | 106 |
| MM (mm) | 20 |
| N (mm) | 8.5 |
| PL (mm) | 21 |
| RT (mm) | M8 |
| R1 (mm) | 74 |
| R2 (mm) | 24 |
| SW (mm) | 17 |
| T (mm) | M8 |
| TG (mm) | 46.5 |
| VA (mm) | 4 |
| VD (mm) | 28 |
| WH (mm) | 37 |
| ZM (mm) | 180 |