

## Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M2V040A0170

Datasheet creation date: 07/03/2025 17:16

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                        |   |
|------------------------|---|
| <b>Series</b>          | 90  |
| <b>Diameter (mm)</b>   | 40  |
| <b>Version</b>         | M = standard magnetic                                       |
| <b>Operation</b>       | 2 = double-acting (front and rear cush.)                    |
| <b>Materials</b>       | V = stainless steel AISI 316 (SS 2343), all joints in viton |
| <b>Construction</b>    | A = standard  |
| <b>Stroke type</b>     | variable  |
| <b>Stroke (mm)</b>     | 170   |
| <b>rod seals viton</b> | -   |

## Stainless steel Cylinders (DIN/ISO 6431 - Series 90)

Product code: 90M2V040A0170



### DIMENSIONS

|         |          |
|---------|----------|
| A (mm)  | 24       |
| B (mm)  | 35       |
| BG (mm) | 16       |
| BF (mm) | 10       |
| E (mm)  | 55       |
| EE      | G1/4     |
| G (mm)  | 31.5     |
| KK      | M12x1,25 |
| L (mm)  | 105      |
| MM (mm) | 16       |
| N (mm)  | 5.5      |
| PL (mm) | 16       |
| RT (mm) | M6       |
| R1 (mm) | 70       |
| R2 (mm) | 21       |
| SW (mm) | 13       |
| T (mm)  | M6       |
| TG (mm) | 38.0     |
| VA (mm) | 4        |
| VD (mm) | 22       |
| WH (mm) | 30       |
| ZM (mm) | 165      |