

## Cylinders - aluminium profile ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 61

Product code: 61M6P040A0120W

Datasheet creation date: 09/03/2025 10:43

Check the most updated document online [click here](#)



### TECHNICAL DATA

|                                      |   |
|--------------------------------------|---|
| <b>SERIE (Series / mm)</b>           | 61  |
| <b>PHY (Diameter / mm)</b>           | 40  |
| <b>VERSION (Version)</b>             | M = magnetic standard   |
| <b>FUNZ (Operation)</b>              | 6=double acting (through-rod with front and rear cushions)  |
| <b>MAT (Materials)</b>               | P = standard: AL end-blocks and piston, rolled stainless steel AISI 420B rod, anodized AL profile tube, zinc-plated steel tie-rods and tie-rod nuts, PU seals |
| <b>TYP (Construction)</b>            | A = standard with lock nut for rod  |
| <b>HUBT (Stroke type)</b>            | variable  |
| <b>HUB (Stroke / mm)</b>             | 120   |
| <b>ES (execution)</b>                | W = all FKM seals +130C°  |
| <b>LSTELO (extended piston / mm)</b> | 0   |

## Cylinders - aluminium profile ISO 15552 (ex DIN/ISO 6431 / VDMA 24562) - Series 61

Product code: 61M6P040A0120W



### DIMENSIONS

|                |          |
|----------------|----------|
| MM (MM / mm)   | 16       |
| KK (KK)        | M12x1,25 |
| B (B d11 / mm) | 35       |
| PL (PL / mm)   | 15       |
| L1 (L1 / mm)   | 21       |
| AM (AM / mm)   | 24       |
| VA (VA / mm)   | -        |
| EE (EE)        | G1/4     |
| WH (WH / mm)   | 30       |
| L2 (L2 / mm)   | 105.0    |
| ZM (ZM / mm)   | 165      |
| ZJ (ZJ / mm)   | -        |
| VD (VD / mm)   | 5        |
| N (N / mm)     | 29.0     |
| BG (BG / mm)   | 16.0     |
| RT (RT)        | M6       |
| G (G / mm)     | 5.0      |
| TG (TG / mm)   | 38.0     |
| R (R / mm)     | 13.5     |
| E (E / mm)     | 55.0     |
| SW1 (SW1 / mm) | 13       |
| SW2 (SW2 / mm) | 6        |
| SW3 (SW3 / mm) | 2        |

|                                    |         |
|------------------------------------|---------|
| SW4 (SW4 / mm)                     | 19      |
| HUBA (Cushion stroke front spring) | 20      |
| HUBP (Cushion stroke rear spring)  | 17      |
| L3 (L3 / mm)                       | 221.5   |
| L4 (L4 / mm)                       | 8       |
| L5 (L5 / mm)                       | 13      |
| L6 (L6 / mm)                       | 22.5    |
| L7 (L7 / mm)                       | 38.0    |
| L8 (L8 / mm)                       | 50      |
| L9 (L9 / mm)                       | 105.0   |
| L10 (/ mm)                         | 178.0   |
| D (ø D / mm)                       | 16      |
| D1 (ø D1 d11 / mm)                 | 35.0    |
| D2 (ø D2 / mm)                     | 40      |
| D3 (ø D3 f6 / mm)                  | 28      |
| A (± 0.15 / mm)                    | 38.0    |
| GX (GX)                            | G1/8    |
| H (H / mm)                         | 30.0    |
| H1 (H1 / mm)                       | 53.0    |
| M (M)                              | M6      |
| Z (Z)                              | M6 x 20 |